

# US-EMLP-HA 30 (45X10) - Plastic label



0803878

<https://www.phoenixcontact.com/us/products/0803878>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, with bore hole, Card, white (RAL 9010), unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: adhesive, Number of individual labels: 4, text field height: 10 mm, text field width: 45 mm



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0803878       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG09          |
| Product key                          | BG2419        |
| GTIN                                 | 4055626173375 |
| Weight per piece (including packing) | 17.09 g       |
| Weight per piece (excluding packing) | 16.93 g       |
| Customs tariff number                | 39199080      |
| Country of origin                    | DE            |

# US-EMLP-HA 30 (45X10) - Plastic label



0803878

<https://www.phoenixcontact.com/us/products/0803878>

## Technical data

### Product properties

|                  |                 |
|------------------|-----------------|
| Product type     | Device marker   |
| Product property | highly adhesive |

### Marking

|                                     |                                    |
|-------------------------------------|------------------------------------|
| Number of individual labels         | 4                                  |
| Number of individual labels per row | 2                                  |
| Identification technology           | Thermotransfer, UV-LED-Technologie |

### Dimensions

|        |          |
|--------|----------|
| Width  | 46.00 mm |
| Height | 47.50 mm |
| Depth  | 0.63 mm  |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 45 mm |
| Text field height | 10 mm |

### Material specifications

|                       |                  |
|-----------------------|------------------|
| Foil strength         | 500 µm           |
| Adhesive strength     | 130 µm           |
| Adhesive              | Acrylic          |
| Color                 | white (RAL 9010) |
| Base element material | PVC              |
| Components            | Silicone-free    |

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -30 °C ... 80 °C  |
| Recommended ambient temperature (storage/transport) | 20 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### Test for substances that would hinder coating with paint or varnish

|   |                         |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result  | Test passed             |

#### Test for substances that would hinder coating with paint or varnish

|   |                      |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result  | Test passed          |

#### Scratch resistance

# US-EMLP-HA 30 (45X10) - Plastic label



0803878

<https://www.phoenixcontact.com/us/products/0803878>

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

## Tesa film test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 100 °C (121 °C) | Test passed                     |

## Wipe resistance of inscriptions

|   |   |
|---|---|
| Specification                                     | DIN EN 61010-1 (VDE 0411-1):2011-07<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                       | Test passed   |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed   |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed   |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed   |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed   |

## Immersion in chemicals, oil & fuel

|   |                          |
|---|--------------------------|
| Specification                                     | ISO 175:2010 (following) |
| Test duration                                     | 168 h                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed              |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ]     | Test passed              |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed              |
| IRM 901   | Test passed              |
| IRM 902   | Test passed              |
| IRM 903   | Test passed              |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                          |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result        | Test passed              |
| Procedure     | Method B                 |

# US-EMLP-HA 30 (45X10) - Plastic label



0803878

<https://www.phoenixcontact.com/us/products/0803878>

|        |   |
|--------|---|
| Cycles | 2 |
|--------|---|

## Salt spray test

|               |   |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h  |

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# US-EMLP-HA 30 (45X10) - Plastic label



0803878

<https://www.phoenixcontact.com/us/products/0803878>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# US-EMLP-HA 30 (45X10) - Plastic label



0803878

<https://www.phoenixcontact.com/us/products/0803878>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.054 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)