

MM-WMS 4,8 (EX9)R C1 WH/BK - Shrink sleeve



0803924

<https://www.phoenixcontact.com/us/products/0803924>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, cable diameter range: 1.6 ... 4.8 mm, mounting type: slide-on, Number of individual labels: 1, roll length: 1.8 m, text field height: 5.4 mm, text field width: 1800 mm

Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- Thanks to the continuous format, a shrink sleeve marker of the appropriate length can be created flexibly for the relevant application
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The shrink sleeve material provides additional electrical insulation and mechanical protection for conductors
- The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- The material is cUL certified

Commercial data

Item number	0803924
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG221E
GTIN	4055626212043
Weight per piece (including packing)	48.7 g
Weight per piece (excluding packing)	46.2 g
Customs tariff number	96121010
Country of origin	CN

MM-WMS 4,8 (EX9)R C1 WH/BK - Shrink sleeve



0803924

<https://www.phoenixcontact.com/us/products/0803924>

Technical data

Product properties

Product type	Shrink sleeve
Area of application	Railway industry

Marking

Number of individual labels	1
Number of individual labels per row	1
Identification technology	Thermal transfer

Dimensions

Length of roll	1.80 m
Height	8.4 mm

Text field

Text field width	1800 mm
Text field height	5.4 mm

Material specifications

Color	white (RAL 9010)
	white (RAL 9010)
Material	Polyolefine
Base element material	polyolefine
Shrink rate	3:1
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	1.6 mm ... 4.8 mm
-------------------------	-------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed

MM-WMS 4,8 (EX9)R C1 WH/BK - Shrink sleeve



0803924

<https://www.phoenixcontact.com/us/products/0803924>

Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

Mounting

Mounting type	slide-on
---------------	----------

MM-WMS 4,8 (EX9)R C1 WH/BK - Shrink sleeve



0803924

<https://www.phoenixcontact.com/us/products/0803924>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0803924>



cULus Recognized
Approval ID: E310982

MM-WMS 4,8 (EX9)R C1 WH/BK - Shrink sleeve



0803924

<https://www.phoenixcontact.com/us/products/0803924>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

MM-WMS 4,8 (EX9)R C1 WH/BK - Shrink sleeve



0803924

<https://www.phoenixcontact.com/us/products/0803924>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.311 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com