

## Zack marker strip - ZBF 6/9,2 S8:UNBEDRUCKT - 0803447

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Zack marker strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 10.5 x 6 mm

### Your advantages

- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 0 5 5 6 2 6 0 7 2 2 0 3
GTIN	4055626072203

### Technical data

#### Dimensions

Length (b)	35 mm
Width (a)	6 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

#### General

Color	white
Type	flat
Components	free from silicone and halogen
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	snap into tall marker groove

### Standards and Regulations

# Zack marker strip - ZBF 6/9,2 S8:UNBEDRUCKT - 0803447

## Technical data

### Standards and Regulations

Flammability rating according to UL 94	V2
----------------------------------------	----

## Classifications

### eCl@ss

eCl@ss 10.0.1	27141137
eCl@ss 11.0	27281101
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27149100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 9.0	27141137

### ETIM

ETIM 6.0	EC000761
ETIM 7.0	EC000761

### UNSPSC

UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505

Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>