

# UBE/D (60X10) - Marker carriers

0803719

<https://www.phoenixcontact.com/us/products/0803719>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Terminal strip marker carrier for identifying terminal groups, for installation on the NS 32 or NS 35/7.5 terminal strips, marking field size: 60 x 10 mm

## Commercial data

Item number	0803719
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG12
Product key	BG211A
GTIN	4055626146263
Weight per piece (including packing)	9.8 g
Weight per piece (excluding packing)	8.035 g
Customs tariff number	39269097
Country of origin	CN

# UBE/D (60X10) - Marker carriers



0803719

<https://www.phoenixcontact.com/us/products/0803719>

## Technical data

### Product properties

Product type	Marker carriers
--------------	-----------------

### Dimensions

Width	12.60 mm
Height	62.60 mm
Depth	45.30 mm

### Text field

Text field width	60 mm
Text field height	10 mm

### Material specifications

RoHS compliant	yes
Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Base element material	PA
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
---------------	-------------------------------------

# UBE/D (60X10) - Marker carriers



0803719

<https://www.phoenixcontact.com/us/products/0803719>

Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Standards and regulations

### Standards

Standards/regulations	EN 45545-2
-----------------------	------------

## Mounting

Mounting type	latching
---------------	----------

# UBE/D (60X10) - Marker carriers



0803719

<https://www.phoenixcontact.com/us/products/0803719>

## Classifications

### ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

### ETIM

ETIM 10.0	EC002248
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UBE/D (60X10) - Marker carriers



0803719

<https://www.phoenixcontact.com/us/products/0803719>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.068 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)