

US-PML-F200 (50X25) - Label



0803868

<https://www.phoenixcontact.com/us/products/0803868>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label, for marking fire detection systems, Card, Mixed color, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0: Rectangle, mounting type: adhesive, Number of individual labels: 10, text field height: 15 mm, text field width: 40 mm



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0803868 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG09 |
| Product key | BG2619 |
| GTIN | 4055626173139 |
| Weight per piece (including packing) | 6.3 g |
| Weight per piece (excluding packing) | 6.3 g |
| Customs tariff number | 39199080 |
| Country of origin | DE |

Technical data

Product properties

| | |
|---------------------|--|
| Product type | Plant marker |
| Area of application | Identification of smoke alarms according to DIN 4066 |

Marking

| | |
|-------------------------------------|------------------|
| Number of individual labels | 10 |
| Number of individual labels per row | 2 |
| Printing | Rectangle |
| Identification technology | Thermal transfer |

Dimensions

| | |
|--------|----------|
| Width | 50.00 mm |
| Height | 25.00 mm |
| Depth | 0.08 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 40 mm |
| Text field height | 15 mm |

Material specifications

| | |
|-----------------------|----------------------|
| Foil strength | 60 µm |
| Adhesive strength | 25 µm |
| Adhesive | Acrylic |
| Color | multicolored (RAL -) |
| | blue (RAL 5015) |
| | white (RAL 9010) |
| Base element material | PVC |
| Components | Silicone-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 22 °C |
| Recommended humidity (storage/transport) | 50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended) |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
|---------------|-------------------------------------|

US-PML-F200 (50X25) - Label



0803868

<https://www.phoenixcontact.com/us/products/0803868>

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 100 °C (121 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|---|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test failed |
| Test duration | 96 h |

Mounting

US-PML-F200 (50X25) - Label

0803868

<https://www.phoenixcontact.com/us/products/0803868>



| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

US-PML-F200 (50X25) - Label



0803868

<https://www.phoenixcontact.com/us/products/0803868>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 40200202 |
| ECLASS-15.0 | 40200202 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001777 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 55121700 |
|-------------|----------|

US-PML-F200 (50X25) - Label



0803868

<https://www.phoenixcontact.com/us/products/0803868>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com