

EML (40X15)R SR - Label



0815729

<https://www.phoenixcontact.com/us/products/0815729>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 2500, text field height: 15 mm, text field width: 40 mm

Your advantages

- The EML ... self-adhesive device markers are particularly suitable for identification of various types of equipment in controller, system, and control cabinet building
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML ... materials are UL-listed
- A wide range of marker sizes and colors are available for custom designs
- Labeling service: Phoenix Contact can custom-label all EM ... markers in accordance with your requirements

Commercial data

Item number	0815729
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG16
Product key	BG2411
GTIN	4046356124324
Weight per piece (including packing)	446.1 g
Weight per piece (excluding packing)	446.1 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	2500
Number of individual labels per row	2
Identification technology	Thermal transfer

Dimensions

Width	40.00 mm
Height	15.00 mm
Depth	0.08 mm

Text field

Text field width	40 mm
Text field height	15 mm

Material specifications

RoHS compliant	yes
Foil strength	50 µm
Adhesive strength	24 µm
Adhesive	Acrylic
Color	silver-colored
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
---------------	--

EML (40X15)R SR - Label



0815729

<https://www.phoenixcontact.com/us/products/0815729>

Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
---	-------------

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Mounting

Mounting type	adhesive
---------------	----------

EML (40X15)R SR - Label



0815729

<https://www.phoenixcontact.com/us/products/0815729>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0815729>



CSA

Approval ID: 70191766



cULus Recognized

Approval ID: MH48542

EML (40X15)R SR - Label



0815729

<https://www.phoenixcontact.com/us/products/0815729>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EML (40X15)R SR - Label



0815729

<https://www.phoenixcontact.com/us/products/0815729>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com