


UC-EMLP (15X5) YE - Plastic label



0822615

<https://www.phoenixcontact.com/us/products/0822615>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plastic label, Sheet, yellow (RAL 1018), unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 5 mm, text field width: 15 mm

Your advantages

- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK printing system
- The UC-EMLP ... UniCard marking range includes self-adhesive device markers with good adhesive properties
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0822615 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG10 |
| Product key | BG2417 |
| GTIN | 4046356328579 |
| Weight per piece (including packing) | 7 g |
| Weight per piece (excluding packing) | 6.985 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

UC-EMLP (15X5) YE - Plastic label



0822615

<https://www.phoenixcontact.com/us/products/0822615>

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

Marking

| | |
|-------------------------------------|-------------------|
| Number of individual labels | 10 |
| Number of individual labels per row | 2 |
| Identification technology | UV LED technology |

Dimensions

| | |
|--------|----------|
| Width | 15.00 mm |
| Height | 5.00 mm |
| Depth | 1.30 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 15 mm |
| Text field height | 5 mm |

Material specifications

| | |
|--|--------------------------------|
| Adhesive strength | 250 µm |
| Adhesive | Acrylic |
| Color | yellow (RAL 1018) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2 |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result | Test passed |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
|---|----------------------|

UC-EMLP (15X5) YE - Plastic label



0822615

<https://www.phoenixcontact.com/us/products/0822615>

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 100 °C (121 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result | Test passed |

UC-EMLP (15X5) YE - Plastic label



0822615

<https://www.phoenixcontact.com/us/products/0822615>

| | |
|-----------|----------|
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Standards

| | |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

UC-EMLP (15X5) YE - Plastic label



0822615

<https://www.phoenixcontact.com/us/products/0822615>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

UC-EMLP (15X5) YE - Plastic label



0822615

<https://www.phoenixcontact.com/us/products/0822615>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.208 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com