

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Carrier for conductor marking collar, unmarked, mounting type: Assembly with cable ties, cable diameter: > 16 mm, text field height: 10 mm, text field width: 92 mm

## Your advantages

- Easy assembly with UNIFOX-CT M7,9
- Secured using stainless steel cable binders
- Cable markers for marking cables and conductors with larger cross sections
- The individual stainless steel markers are pushed onto the corresponding holders

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0826598       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BG12          |
| Product key                          | BG231A        |
| GTIN                                 | 4046356412964 |
| Weight per piece (including packing) | 2.606 g       |
| Weight per piece (excluding packing) | 2.596 g       |
| Customs tariff number                | 83100000      |
| Country of origin                    | SE            |

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

## Technical data

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

### Dimensions

|        |       |
|--------|-------|
| Width  | 10 mm |
| Length | 92 mm |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 92 mm |
| Text field height | 10 mm |

### Material specifications

|                       |                 |
|-----------------------|-----------------|
| Color                 | silver-colored  |
| Material              | Stainless steel |
| Base element material | Stainless steel |

### Cable/line

|                         |            |
|-------------------------|------------|
| External cable diameter | > 16.00 mm |
|-------------------------|------------|

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -80 °C ... 400 °C   |
| Recommended ambient temperature (storage/transport) | 23 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

#### Tesafilm test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

#### Wipe resistance of inscriptions

|               |  |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07            |
|               | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

|   |             |
|---|-------------|
| Isopropanol (99%) [67-63-0]                     | Test passed |
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed |

## Immersion in chemicals, oil & fuel

|   |                          |
|---|--------------------------|
| Specification                                 | ISO 175:2010 (following) |
| Test duration                                 | 168 h                    |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ] | Test passed              |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |                          |
|---------------|--------------------------|
| Mounting type | Assembly with cable ties |
|---------------|--------------------------|

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)