

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Carrier for conductor marking collar, unmarked, mounting type: Assembly with cable ties, cable diameter: > 16 mm, text field height: 10 mm, text field width: 92 mm

## Your advantages

- Easy assembly with UNIFOX-CT M7,9
- Secured using stainless steel cable binders
- Cable markers for marking cables and conductors with larger cross sections
- The individual stainless steel markers are pushed onto the corresponding holders

## Commercial data

Item number	0826598
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG12
Product key	BG231A
GTIN	4046356412964
Weight per piece (including packing)	2.606 g
Weight per piece (excluding packing)	2.596 g
Customs tariff number	83100000
Country of origin	SE

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

## Technical data

### Product properties

Product type	Marker carriers
--------------	-----------------

### Dimensions

Width	10 mm
Length	92 mm

### Text field

Text field width	92 mm
Text field height	10 mm

### Material specifications

Color	silver-colored
Material	Stainless steel
Base element material	Stainless steel

### Cable/line

External cable diameter	> 16.00 mm
-------------------------	------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-80 °C ... 400 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 10.0	EC001530
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# SD-WMTB (92X10) VA - Carrier for conductor marking collar



0826598

<https://www.phoenixcontact.com/us/products/0826598>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)