

UCT1-TMF 6 RD - Marker for terminal blocks



0829244

<https://www.phoenixcontact.com/us/products/0829244>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

UniCard materials for thermal transfer printers, for labeling Weidmüller, Conta Clip, and Klemsan terminal blocks with horizontal marker groove, 60-section, can be labeled with THERMOMARK CARD and BLUEMARK LED, color: red



Your advantages

- The UCT1-TMF ... UniCard labeling range includes markers for Weidmüller, Wago, ABB (entrelec), Conta-Clip, and Klemsan terminal blocks
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0829244 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG07 |
| Product key | BG2118 |
| GTIN | 4046356596398 |
| Weight per piece (including packing) | 10.22 g |
| Weight per piece (excluding packing) | 10 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

UCT1-TMF 6 RD - Marker for terminal blocks



0829244

<https://www.phoenixcontact.com/us/products/0829244>

Technical data

Product properties

| | |
|---------------------|---|
| Product type | Terminal marker |
| Area of application | Weidmüller, Wago, ABB, CONTA-CLIP, and Klemsan: Terminal blocks |
| Pitch | 6.2 mm |

Marking

| | |
|-------------------------------------|---|
| Number of individual labels | 60 |
| Number of individual labels per row | 10 |
| Slot type | flat |
| Identification technology | Thermotransfer, UV-LED-Technologie, Laserdirektbeschriftung |

Dimensions

| | |
|--------|---------|
| Width | 5.45 mm |
| Height | 5.20 mm |
| Depth | 2.40 mm |
| Pitch | 6.2 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 5.45 mm |
| Text field height | 5.2 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | flame red (RAL 3000) |
| Flammability rating according to UL 94 | V0 |
| Base element material | PC |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result | Test passed |

Test for substances that would hinder coating with paint or varnish

UCT1-TMF 6 RD - Marker for terminal blocks



0829244

<https://www.phoenixcontact.com/us/products/0829244>

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 100 °C (121 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result | Test passed |

UCT1-TMF 6 RD - Marker for terminal blocks



0829244

<https://www.phoenixcontact.com/us/products/0829244>

| | |
|-----------|----------|
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Standards

| | |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

UCT1-TMF 6 RD - Marker for terminal blocks



0829244

<https://www.phoenixcontact.com/us/products/0829244>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

UCT1-TMF 6 RD - Marker for terminal blocks



0829244

<https://www.phoenixcontact.com/us/products/0829244>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.057 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com