

TMC 61C 40A - Thermal-magnetic device circuit breaker



0902137

<https://www.phoenixcontact.com/us/products/0902137>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal-magnetic circuit breaker, one-pole, 40 A thermal trip. DIN rail mounted and UL 1077-recognized with optional auxiliary contact for either S or H remote signal. Protects wiring and equipment from overcurrent and short circuit faults.

Commercial data

Item number	0902137
Packing unit	12 pc
Minimum order quantity	12 pc
Note	Made to order (non-returnable)
Sales key	CL04
Product key	CLA121
GTIN	4046356557917
Weight per piece (including packing)	144.3 g
Weight per piece (excluding packing)	125 g
Customs tariff number	85362010
Country of origin	HU

TMC 61C 40A - Thermal-magnetic device circuit breaker



0902137

<https://www.phoenixcontact.com/us/products/0902137>

Technical data

Product properties

Product type	Thermomagnetic device circuit breakers
Product family	TMC
Number of positions	1
Mechanical service life	20000

Electrical properties

Service life electrical	10000
Maximum current with single arrangement	40 A

General

Operating voltage	277 V AC (UL 1077)
	240 V AC ($I_{CS} = 15 \text{ kA}$ (IEC 60947-2))
	415 V AC ($I_{CS} = 4 \text{ kA}$ (IEC 60947-2))
	60 V DC
	12 V
Rated current I_N	40 A
Tripping method	C
Rated short-circuit switching capacity I_{cn}	10 kA (IC)
Fuse	circuit-breaker C
Contact switching type	none

Connection data

Connection method	Biconnect terminal blocks
Tightening torque	2.5 Nm ... 4.5 Nm (Torque can be application dependent with changes in temperature, vibration, and wire size. For additional assistance, contact Customer Service.)
Stripping length	12 mm
Conductor cross-section flexible min.	1 mm ²
Conductor cross-section flexible max.	35 mm ²

Dimensions

Width	18 mm
Height	86 mm

Material specifications

Flammability rating according to UL 94	V0
--	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-55 °C ... 55 °C

TMC 61C 40A - Thermal-magnetic device circuit breaker



0902137

<https://www.phoenixcontact.com/us/products/0902137>

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

TMC 61C 40A - Thermal-magnetic device circuit breaker



0902137

<https://www.phoenixcontact.com/us/products/0902137>

Classifications

UNSPSC

UNSPSC 21.0	39121410
-------------	----------

TMC 61C 40A - Thermal-magnetic device circuit breaker



0902137

<https://www.phoenixcontact.com/us/products/0902137>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-25 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com