


UC-PMP (90X38) BU - Insert label

0831048

<https://www.phoenixcontact.com/us/products/0831048>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert label, Sheet, blue (RAL 5015), unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, mounting type: snapped into marker carrier, text field height: 38 mm, text field width: 90 mm



Your advantages

- The UC-PMP ... plant identification family includes markers that can be mounted in existing CARRIER...-PMP... marker carriers
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0831048 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG12 |
| Product key | BG261B |
| GTIN | 4046356940795 |
| Weight per piece (including packing) | 9.63 g |
| Weight per piece (excluding packing) | 9.63 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

UC-PMP (90X38) BU - Insert label



0831048

<https://www.phoenixcontact.com/us/products/0831048>

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | Plant marker |
|--------------|--------------|

Marking

| | |
|---------------------------|-------------------|
| Identification technology | UV LED technology |
|---------------------------|-------------------|

Dimensions

| | |
|--------|----------|
| Width | 90.00 mm |
| Height | 38.00 mm |
| Depth | 1.15 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 90 mm |
| Text field height | 38 mm |

Material specifications

| | |
|---|--------------------------------|
| RoHS compliant | yes |
| Color | blue (RAL 5015) |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 120 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2 |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result | Test passed |
| Test duration | 96 h |

Wipe resistance of inscriptions

UC-PMP (90X38) BU - Insert label



0831048

<https://www.phoenixcontact.com/us/products/0831048>

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result | Test passed |
| Climate level | AHT 1.0 S |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result | Test passed |

Mounting

| | |
|---------------|-----------------------------|
| Mounting type | snapped into marker carrier |
|---------------|-----------------------------|

UC-PMP (90X38) BU - Insert label



0831048

<https://www.phoenixcontact.com/us/products/0831048>

Classifications

ECLASS

ECLASS-13.0

27281104

ETIM

ETIM 9.0

EC001288

UNSPSC

UNSPSC 21.0

39131500

UC-PMP (90X38) BU - Insert label



0831048

<https://www.phoenixcontact.com/us/products/0831048>

Environmental product compliance

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.13 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com