

# LS-WMTB-V4A (100X15) - Cable marker



0831519

<https://www.phoenixcontact.com/us/products/0831519>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Stainless steel label, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: Assembly with cable ties, cable diameter: > 4.6 mm, Number of individual labels: 8, text field height: 15 mm, text field width: 100 mm



## Your advantages

- Stainless steel cable marking for assembly with cable ties
- Easy-to-clean and permanent identification that also meets stringent hygiene requirements
- High resistance to corrosion, acids, and temperatures
- Suitable for large-surface marking of wires and cables, > 2.9 mm in diameter

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0831519       |
| Packing unit                         | 5 pc          |
| Minimum order quantity               | 5 pc          |
| Sales key                            | BG19          |
| Product key                          | BG231D        |
| GTIN                                 | 4046356925297 |
| Weight per piece (including packing) | 100.26 g      |
| Weight per piece (excluding packing) | 100.26 g      |
| Customs tariff number                | 73269098      |
| Country of origin                    | CN            |

# LS-WMTB-V4A (100X15) - Cable marker



0831519

<https://www.phoenixcontact.com/us/products/0831519>

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
| Type         | Rectangle        |

### Marking

|                             |                      |
|-----------------------------|----------------------|
| Number of individual labels | 8                    |
| Identification technology   | Direct laser marking |

### Dimensions

|        |        |
|--------|--------|
| Width  | 118 mm |
| Height | 15 mm  |
| Depth  | 0.5 mm |

### Text field

|                   |        |
|-------------------|--------|
| Text field width  | 100 mm |
| Text field height | 15 mm  |

### Material specifications

|                       |  |
|-----------------------|--|
| Color                 | silver-colored                           |
| Base element material | V4A (1.4404; AISI 316L)                  |
| Components            | free from silicone, halogen, and cadmium |

### Cable/line

|                         |           |
|-------------------------|-----------|
| External cable diameter | > 4.60 mm |
|-------------------------|-----------|

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -80 °C ... 350 °C   |
| Recommended ambient temperature (storage/transport) | 23 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### Test for substances that would hinder coating with paint or varnish

|   |                      |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result  | Test passed          |

#### Test for substances that would hinder coating with paint or varnish

|   |                         |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result  | Test passed             |

#### Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
|---------------|--------------------------------|

# LS-WMTB-V4A (100X15) - Cable marker



0831519

<https://www.phoenixcontact.com/us/products/0831519>

|              |             |
|--------------|-------------|
| Requirements | ≥ 5 N       |
| Result       | Test passed |

## Tesafilm test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Temperature storage

|                         |                       |
|-------------------------|-----------------------|
| Specification           | IEC 60068-2-2:2007-07 |
| Result                  | Test passed           |
| Procedure               | Test Bb               |
| Duration                | 240 h                 |
| Temperature for testing | 350 °C                |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 225 °C (250 °C) | Test passed                     |

## Wipe resistance of inscriptions

|   |   |
|---|---|
| Specification                                     | DIN EN 61010-1 (VDE 0411-1):2011-07<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                       | Test passed   |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed   |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed   |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed   |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed   |
| Acetone (99 %)<br>[CAS No. 67-64-1]               | Test passed   |

## Immersion in chemicals, oil & fuel

|   |                          |
|---|--------------------------|
| Specification                                 | ISO 175:2010 (following) |
| Test duration                                 | 168 h                    |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ] | Test passed              |
| Ethanol (99 %)<br>[CAS No. 64-17-5]           | Test passed              |
| Acetone (99 %)<br>[CAS No. 67-64-1]           | Test passed              |

# LS-WMTB-V4A (100X15) - Cable marker



0831519

<https://www.phoenixcontact.com/us/products/0831519>

|  |             |
|--|-------------|
| Methylethylketone (MEK)<br>[CAS No. 78-93-3] | Test passed |
| IRM 901                                      | Test passed |
| IRM 902                                      | Test passed |
| IRM 903                                      | Test passed |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                          |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result        | Test passed              |
| Procedure     | Method B                 |
| Cycles        | 2                        |

## Salt spray test

|               |   |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h  |

## Salt spray test

|               |                  |
|---------------|------------------|
| Specification | ISO 9227:2017-03 |
| Result        | Test passed      |
| Test duration | 336 h            |

## High pressure test

|               |                   |
|---------------|-------------------|
| Specification | ISO 20653:2013-02 |
| Result        | Test passed       |
| IP-Code       | IP X9K            |

## Mounting

|               |                          |
|---------------|--------------------------|
| Mounting type | Assembly with cable ties |
|---------------|--------------------------|

# LS-WMTB-V4A (100X15) - Cable marker



0831519

<https://www.phoenixcontact.com/us/products/0831519>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# LS-WMTB-V4A (100X15) - Cable marker



0831519

<https://www.phoenixcontact.com/us/products/0831519>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)