

# LS-EMLP-AL (85,6X54) - Device marker



0831585

<https://www.phoenixcontact.com/us/products/0831585>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Aluminum label, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 6, text field height: 54 mm, text field width: 85.6 mm



## Your advantages

- Aluminum equipment marking for sticking on
- Identification made from metal, high strength in a lightweight design
- Increased durability due to the decoratively anodized surface

## Commercial data

Item number	0831585
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG19
Product key	BG241D
GTIN	4046356925389
Weight per piece (including packing)	103.688 g
Weight per piece (excluding packing)	81.74 g
Customs tariff number	76169990
Country of origin	CN

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	6
Identification technology	Direct laser marking

### Dimensions

Width	85.00 mm
Height	53.70 mm
Depth	1.05 mm

### Text field

Text field width	85.6 mm
Text field height	54 mm

### Material specifications

Foil strength	800 µm
Adhesive strength	250 µm
Adhesive	Acrylic
Color	aluminum color
Base element material	Aluminum
Components	free from silicone, halogen, and cadmium

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 120 °C (At temperatures above 80 °C there might be a slight change to the material surface)
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

#### Wipe resistance of inscriptions

# LS-EMLP-AL (85,6X54) - Device marker



0831585

<https://www.phoenixcontact.com/us/products/0831585>

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

## High pressure test

Specification	ISO 20653:2013-02
Result	Test passed
IP-Code	IP X9K

## Mounting

Mounting type	adhesive
---------------	----------

# LS-EMLP-AL (85,6X54) - Device marker



0831585

<https://www.phoenixcontact.com/us/products/0831585>

## Classifications

### ECLASS

ECLASS-15.0	27281103
ECLASS-13.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# LS-EMLP-AL (85,6X54) - Device marker



0831585

<https://www.phoenixcontact.com/us/products/0831585>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)