

PML-W400 (58/19XE)R WH-OG - Warning label



1016499

<https://www.phoenixcontact.com/us/products/1016499>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Warning label, Mixed color, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, mounting type: adhesive, text field height: 77 mm, text field width: 48000 mm

Your advantages

- Stick-on warning label, color preprinted
- Highly flexible, soft PVC label that adapts well to uneven surfaces
- Continuous media which can be cut to the desired length with the cutting unit on the printer or manually with scissors
- When high-quality ink ribbons are used, the marking is resistant to solvents and suitable for use even under harsh industrial conditions.
- A temperature range of -50 °C ... 90 °C

Commercial data

Item number	1016499
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG21
Product key	BG2611
GTIN	4055626497150
Weight per piece (including packing)	1,246.8 g
Weight per piece (excluding packing)	1,229.7 g
Customs tariff number	49119900
Country of origin	DE

PML-W400 (58/19XE)R WH-OG - Warning label



1016499

<https://www.phoenixcontact.com/us/products/1016499>

Technical data

Product properties

Product type	Plant marker
Area of application	Warning labels
	Notice marking according to ISO 3864 and ANSI Z535

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Dimensions

Height	77 mm
--------	-------

Text field

Text field width	48000 mm
Text field height	77 mm

Material specifications

Foil strength	60 µm
Adhesive strength	25 µm
Adhesive	Acrylic
Color	multicolored (RAL -)
	white (RAL 9010)
	orange (RAL 2003)
Material	PVC
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
---------------	-------------------------------------

PML-W400 (58/19XE)R WH-OG - Warning label



1016499

<https://www.phoenixcontact.com/us/products/1016499>

Result	Test passed
--------	-------------

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	87 °C

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

PML-W400 (58/19XE)R WH-OG - Warning label



1016499

<https://www.phoenixcontact.com/us/products/1016499>

Classifications

ECLASS

ECLASS-13.0	40200203
ECLASS-15.0	40200203

ETIM

ETIM 10.0	EC001777
-----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

PML-W400 (58/19XE)R WH-OG - Warning label



1016499

<https://www.phoenixcontact.com/us/products/1016499>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com