

# TMCP SOCKET M - Surface mounting housing



0916589

<https://www.phoenixcontact.com/us/products/0916589>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Modular socket element, 2-position, for holding two circuit breakers, each with a single position



## Your advantages

- Fast installation with reduced wiring work with bridging options
- Can be extended at any time with the modular design
- Automatic group remote signaling setup with integrated remote messaging system

## Commercial data

Item number	0916589
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	CL04
Product key	CLA191
GTIN	4017918600921
Weight per piece (including packing)	108.2 g
Weight per piece (excluding packing)	97 g
Customs tariff number	85366990
Country of origin	DE

# TMCP SOCKET M - Surface mounting housing



0916589

<https://www.phoenixcontact.com/us/products/0916589>

## Technical data

### Product properties

Product type	Base element
Type	Surface mounting housing
Number of connections	2
Number of rows	1

### Insulation characteristics

Degree of pollution	2
---------------------	---

### Electrical properties

Fuse type	Automatic device
Rated surge voltage	2.5 kV
Maximum power dissipation for nominal condition	0 VA

### General

Operating voltage	433 V (AC)
Nominal current $I_N$	50 A (LINE input)
	25 A (LOAD output)
Rated voltage	433 V (AC)
	65 V (DC)
Rated insulation voltage $U_i$	1500 V
Rated current $I_N$	50 A
Rated surge voltage	2.5 kV
Type of actuation	N/C contact and N/O contact

### Auxiliary contact

Connection name	Input
Maximum operating voltage $U_{max}$ DC	65 V
Maximum operating voltage $U_{max}$ AC	250 V (AC)
Max. operating current $I_{max}$	10 A (Input)

### Auxiliary contact

Connection name	Output
Maximum operating voltage $U_{max}$ DC	65 V (DC)
Maximum operating voltage $U_{max}$ AC	250 V (AC)
Max. operating current $I_{max}$	1 A

### Reset

Input voltage	24 V (Falling edge)
---------------	---------------------

### Connection data

Connection method	Spring-cage connection
Connection method	Spring-cage connection

# TMCP SOCKET M - Surface mounting housing



0916589

<https://www.phoenixcontact.com/us/products/0916589>

## Input

Connection method	Spring-cage connection
Stripping length	15 mm
Conductor cross-section flexible min.	1.5 mm <sup>2</sup>
Conductor cross-section flexible max.	10 mm <sup>2</sup>
Conductor cross-section, rigid min.	1.5 mm <sup>2</sup>
Conductor cross-section, rigid max.	10 mm <sup>2</sup>

## Output

Connection method	Spring-cage connection
Stripping length	12 mm
Conductor cross-section flexible min.	0.25 mm <sup>2</sup>
Conductor cross-section flexible max.	4 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.25 mm <sup>2</sup>
Conductor cross-section, rigid max.	4 mm <sup>2</sup>

## Signal level

Connection method	Spring-cage connection
Stripping length	10 mm
Conductor cross-section flexible min.	0.25 mm <sup>2</sup>
Conductor cross-section flexible max.	2.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.25 mm <sup>2</sup>
Conductor cross-section, rigid max.	2.5 mm <sup>2</sup>

## Signal level

Connection method	Spring-cage connection
Stripping length	10 mm
Conductor cross-section flexible min.	0.25 mm <sup>2</sup>
Conductor cross-section flexible max.	1.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.25 mm <sup>2</sup>
Conductor cross-section, rigid max.	1.5 mm <sup>2</sup>

## Dimensions

Width	25 mm
Height	115 mm
Height NS 35/15	118 mm
Height NS 35/7,5	110.5 mm
Depth	110.5 mm

## Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Insulating material	PA-F

## Mechanical properties

# TMCP SOCKET M - Surface mounting housing



0916589

<https://www.phoenixcontact.com/us/products/0916589>

## Mechanical data

Open side panel

Yes

## Mounting

Mounting type

DIN rail: 35 mm

# TMCP SOCKET M - Surface mounting housing



0916589

<https://www.phoenixcontact.com/us/products/0916589>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0916589>



**cUL Recognized**  
Approval ID: FILE E 337423



**UL Recognized**  
Approval ID: FILE E 337423

# TMCP SOCKET M - Surface mounting housing



0916589

<https://www.phoenixcontact.com/us/products/0916589>

## Classifications

### ECLASS

ECLASS-13.0	27140492
ECLASS-15.0	27140492

### ETIM

ETIM 10.0	EC002936
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# TMCP SOCKET M - Surface mounting housing



0916589

<https://www.phoenixcontact.com/us/products/0916589>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	1.85 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)