

# CK1,6-BR-1,00ST OIC AG - Crimp contact



1004380

<https://www.phoenixcontact.com/us/products/1004380>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, Pin, rolled, contact diameter: 1.6 mm, connection cross section: 0.34 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 22...17, contact material: Cu alloy

## Commercial data

Item number	1004380
Packing unit	7,000 pc
Minimum order quantity	7,000 pc
Sales key	BF65
Product key	AF7AIB
GTIN	4055626472393
Weight per piece (including packing)	0.66 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85366990
Country of origin	TR

# CK1,6-BR-1,00ST OIC AG - Crimp contact



1004380

<https://www.phoenixcontact.com/us/products/1004380>

## Technical data

### Notes

Assembly note	max. crimping speed for 1 mm <sup>2</sup> corresponds to a cycle time of 1 second
Assembly note	Note on crimp connection technology:  For flexible wires only. The specified conductor cross-sections refer to the nominal cross-section of the cable used.  The wiring space of the crimp connection technology is designed for fine-stranded cables in accordance with VDE 0295 Class 5. Deviating cable structures (e.g., Class 1.2 and 6 or AWG cables) should be checked before use.

### Product properties

Product type	Crimp contact
Contact material type	rolled

### Connection data


Connection technology	
Contact connection type	Pin
Connection method	Crimp connection

Conductor connection	
Stripping length	4 mm
Connection cross section	0.34 mm <sup>2</sup> ... 1 mm <sup>2</sup>
Connection cross section AWG	22 ... 17

### Material specifications

Material Contact	Cu alloy (nickel-plated)
Material Contact surface	Ag

### Dimensions

Dimensional drawing	
Length [l]	24.5 mm
Diameter (Contact diameter)	1.6 mm

### Mechanical properties

# CK1,6-BR-1,00ST OIC AG - Crimp contact



1004380

<https://www.phoenixcontact.com/us/products/1004380>

## Mechanical data

Insertion/withdrawal cycles

≥ 50

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)

-40 °C ... 125 °C


# CK1,6-BR-1,00ST OIC AG - Crimp contact



1004380

<https://www.phoenixcontact.com/us/products/1004380>

## Drawings



# CK1,6-BR-1,00ST OIC AG - Crimp contact



1004380

<https://www.phoenixcontact.com/us/products/1004380>

## Classifications

### ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

### ETIM

ETIM 10.0	EC000796
-----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# CK1,6-BR-1,00ST OIC AG - Crimp contact



1004380

<https://www.phoenixcontact.com/us/products/1004380>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)