

# SAC-4P-M12MRT/ 0,8-PUR/M12FRT - Power cable



1012017

<https://www.phoenixcontact.com/us/products/1012017>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Power cable, 4-position, PUR halogen-free, black-gray RAL 7021, Plug angled M12, coding: T, on Socket angled M12, coding: T, cable length: 0.8 m, For direct current up to 12 A/63 V



## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against incorrect connection using special T-coding
- Our standard: robust halogen-free PUR cable

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1012017       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 50 pc         |
| Product key                          | AF1CCQ        |
| GTIN                                 | 4055626487342 |
| Weight per piece (including packing) | 146.31 g      |
| Weight per piece (excluding packing) | 146.31 g      |
| Country of origin                    | PL            |

1012017

<https://www.phoenixcontact.com/us/products/1012017>

## Technical data

### Product properties

|                      |               |
|----------------------|---------------|
| Product type         | Power cable   |
| Application          | Energy supply |
| Number of positions  | 4             |
| No. of cable outlets | 1             |
| Shielded             | no            |
| Coding               | T             |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Material specifications

|  |                              |
|--|------------------------------|
| Flammability rating according to UL 94 | V0                           |
| Material of grip body                  | PP                           |
| Contact material                       | CuZn                         |
| Contact surface material               | Ni/Au                        |
| Contact carrier material               | PA                           |
| Material for screw connection          | Zinc die-cast, nickel-plated |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 63 V DC                    |
| Nominal current $I_N$ | 12 A                       |

### Mechanical properties

#### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

### Connector

#### Connection 1

|             |                 |
|-------------|-----------------|
| Type        | Plug angled M12 |
| Coding type | T (Power)       |

#### Connection 2

|             |                   |
|-------------|-------------------|
| Type        | Socket angled M12 |
| Coding type | T (Power)         |

### Cable/line

|              |       |
|--------------|-------|
| Cable length | 0.8 m |
|--------------|-------|


PUR halogen-free black [PUR]

# SAC-4P-M12MRT/ 0,8-PUR/M12FRT - Power cable



1012017

<https://www.phoenixcontact.com/us/products/1012017>

|   |  |
|---|--|
| Dimensional drawing                           |    |
| Cable weight                                  | 83 kg/km   |
| UL AWM Style                                  | 20549 / 10493 (80°C/300 V)   |
| Number of positions                           | 4  |
| Shielded                                      | no   |
| Cable type                                    | PUR halogen-free black [PUR]   |
| Conductor structure, voltage supply           | 44x 0.20 mm  |
| AWG power supply                              | 16   |
| Conductor cross-section                       | 4x 1.5 mm <sup>2</sup>   |
| Wire diameter incl. insulation                | 2.2 mm ±0.05 mm  |
| External cable diameter                       | 6.75 mm ±0.2 mm  |
| Outer sheath, material                        | PUR  |
| External sheath, color                        | black-gray RAL 7021  |
| Conductor material                            | Bare Cu litz wires   |
| Material wire insulation                      | PP   |
| Single wire, color                            | brown, white, blue, black  |
| Thickness, insulation                         | ≥ 0.26 mm  |
| Thickness, outer sheath                       | approx. 0.70 mm  |
| Overall twist                                 | 4 wires, twisted   |
| Max. conductor resistance                     | ≤ 14.1 Ω/km (at 20 °C)   |
| Insulation resistance                         | ≥ 1 GΩ*km (at 20 °C)   |
| Nominal voltage, cable                        | ≤ 300 V AC   |
| Test voltage                                  | ≥ 3000 V AC (Spark test)   |
| Minimum bending radius, fixed installation    | 5 x D  |
| Minimum bending radius, flexible installation | 10 x D   |
| Smallest bending radius, fixed installation   | 34 mm  |
| Smallest bending radius, movable installation | 68 mm  |
| Dynamic load capacity (bending)               | Max. bending cycles: 5000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup> |
| Dynamic load capacity (torsion)               | Torsion: ±180 °/m, Torsion cycles: 500000, Torsional frequency: 35 cycles/min.   |
| Halogen-free                                  | in accordance with DIN VDE 0472 part 815<br>in accordance with DIN EN 50267-2-1  |
| Flame resistance                              | According to UL 758/1581 (Cable Flame)<br>in accordance with UL 758/1581 FT2<br>according to DIN EN 60332-2-2                          |

# SAC-4P-M12MRT/ 0,8-PUR/M12FRT - Power cable



1012017

<https://www.phoenixcontact.com/us/products/1012017>

|                                 |   |
|---------------------------------|---|
| Resistance to oil               | according to DIN EN 60811-404, 168 h at 100 °C              |
|                                 | according to UL 758, 168 h at 60 °C                         |
| Other resistance                | Hydrolysis and microbe resistant as per VDE 0282 section 10 |
|                                 | Low adhesion  |
|                                 | abrasion-resistant  |
|                                 | Resistant to salt water                                     |
| Special properties              | Flexible cable conduit capable                              |
| Ambient temperature (operation) | -50 °C ... 85 °C (cable, fixed installation)                |
|                                 | -30 °C ... 85 °C (Cable, flexible installation)             |

## Environmental and real-life conditions

### Ambient conditions

|   |                                  |
|---|----------------------------------|
| Degree of protection  | IP65                             |
|   | IP67                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-111 |


Drawings

Dimensional drawing



M12 x 1 male plug, angled

Dimensional drawing



M12 x 1 socket, angled

1012017

<https://www.phoenixcontact.com/us/products/1012017>

Schematic diagram




Pin assignment for M12 plug, 4-pos., T-coded, view of plug side

Schematic diagram



Pin assignment of M12 socket, 4-pos., T-coded, socket side view



Base curve

Circuit diagram



Contact assignment of M12 connector/socket

# SAC-4P-M12MRT/ 0,8-PUR/M12FRT - Power cable



1012017

<https://www.phoenixcontact.com/us/products/1012017>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060327 |
| ECLASS-15.0 | 27060327 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31251501 |
|-------------|----------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)