

SAC-2P-MSB/1,7-910/FSB SCO CT - Bus system cable



1022061

<https://www.phoenixcontact.com/us/products/1022061>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, PROFIBUS, 2-pos., halogen-free PUR, purple RAL 4001, shielded, straight M12 SPEEDCON male plug, B-coded, on straight M12 SPEEDCON female plug, cable length: 7.5 m, customer version

Commercial data

Item number	1022061
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CJC
GTIN	4055626515052
Weight per piece (including packing)	138.3 g
Weight per piece (excluding packing)	134.034 g
Country of origin	PL

SAC-2P-MSB/1,7-910/FSB SCO CT - Bus system cable



1022061

<https://www.phoenixcontact.com/us/products/1022061>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	PROFIBUS
Number of positions	2
No. of cable outlets	1
Shielded	yes
Coding	B

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Interfaces

Bus system	PROFIBUS
Signal type/category	PROFIBUS

Signaling

Status display	no
Status display present	no

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Connector

Connection 1

SAC-2P-MSB/1,7-910/FSB SCO CT - Bus system cable



1022061

<https://www.phoenixcontact.com/us/products/1022061>

Type	Plug straight M12 SPEEDCON
Number of positions	2
Locking type	SPEEDCON
Coding type	B (inverse)


Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	2
Locking type	SPEEDCON

Cable/line

Cable length	1.7 m
--------------	-------

PROFIBUS [910]

Dimensional drawing	
UL AWM Style	21198 (80°C/300 V)
Number of positions	2
Shielded	yes
Cable type	PROFIBUS [910]
Conductor structure	1x2xAWG24/19
AWG signal line	24
Conductor cross-section	2x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	2.55 mm ±0.05 mm
External cable diameter	7.70 mm ±0.02 mm
Outer sheath, material	PUR
External sheath, color	red lilac RAL 4001
Conductor material	Tin-plated Cu litz wires
Single wire, color	red, green
Overall twist	2 cores with 2 fillers to the core
Optical shield covering	80 %
Insulation resistance	≥ 5 GΩ*km
Wave impedance	150 Ω ±10 % (3 MHz ... 20 MHz)
Nominal voltage, cable	≤ 125 V
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Dynamic load capacity (bending)	Max. bending cycles: 4000000, Bending radius: 65 mm, Bending

SAC-2P-MSB/1,7-910/FSB SCO CT - Bus system cable



1022061

<https://www.phoenixcontact.com/us/products/1022061>

	radius: 15 x D, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 3 m/s ²
Shield attenuation	≤ 4.9 dB (at 16 MHz)
	≤ 4.9 dB (at 4 MHz)
	≤ 0.5 dB (at 38.4 kHz)
	≤ 0.3 dB (at 9.6 kHz)
Halogen-free	in accordance with DIN VDE 0472 part 815
	according to IEC 60754-1
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
	IEC 60332-1-2
Resistance to oil	in accordance with DIN EN 60811-404
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-30 °C ... 70 °C (Cable, flexible installation)
	-20 °C ... 60 °C (for installation)
	-20 °C ... 60 °C (cable, drag chain applications)

SAC-2P-MSB/1,7-910/FSB SCO CT - Bus system cable

1022061

<https://www.phoenixcontact.com/us/products/1022061>

Drawings

Dimensional drawing



M12 SPEEDCON plug, straight, shielded

Dimensional drawing



Socket M12-SPEEDCON, straight, shielded

1022061


<https://www.phoenixcontact.com/us/products/1022061>

Schematic diagram



Pin assignment M12 male connector, 5-pos., B-coded, male side

Circuit diagram



SAC-2P-MSB/1,7-910/FSB SCO CT - Bus system cable



1022061

<https://www.phoenixcontact.com/us/products/1022061>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

UNSPSC

UNSPSC 21.0	26121604
-------------	----------

SAC-2P-MSB/1,7-910/FSB SCO CT - Bus system cable



1022061

<https://www.phoenixcontact.com/us/products/1022061>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com