

NBC-MRD/ 1,0-93K/FSD SCO - Network cable



1026097

<https://www.phoenixcontact.com/us/products/1026097>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Sercos CAT5 (100 Mbps), 4-position, shielded, Plug angled M12 SPEEDCON, coding: D / IP67, on Socket straight M12 SPEEDCON, coding: D / IP67, cable length: 1 m

Commercial data

Item number	1026097
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CJO
GTIN	4055626519319
Weight per piece (including packing)	105.3 g
Weight per piece (excluding packing)	105.3 g
Country of origin	PL

1026097

<https://www.phoenixcontact.com/us/products/1026097>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	Sercos
Number of positions	4

Interfaces

Signal type/category	Sercos CAT5, 100 Mbps
----------------------	-----------------------

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Transmission speed	100 Mbps

Material specifications

Outer sheath, material	PVC
------------------------	-----

Connector

Connection 1

Type	Plug angled M12 SPEEDCON / IP67
Number of positions	4
Locking type	SPEEDCON
Coding type	D (Data)
Handle color	black
Material	CuSn (Contact)
	TPU, hardly inflammable, self-extinguishing (Grip body)
	Zinc die-cast, nickel-plated (Screw connection)
Insertion/withdrawal cycles	≥ 100
Insulation resistance	≥ 100 MΩ
Tightening torque	0.4 Nm
Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 90 °C

Connection 2

Type	Socket straight M12 SPEEDCON / IP67
Number of positions	4
Locking type	SPEEDCON
Coding type	D (Data)
Handle color	black
Material	CuSn (Contact)
	Ni/Au (Contact surface)
	TPU GF (Contact carrier)
	TPU, hardly inflammable, self-extinguishing (Grip body)

NBC-MRD/ 1,0-93K/FSD SCO - Network cable



1026097

<https://www.phoenixcontact.com/us/products/1026097>

	Zinc die-cast, nickel-plated (Screw connection)
Insertion/withdrawal cycles	≥ 100
Insulation resistance	≥ 100 MΩ
Tightening torque	0.4 Nm
Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 90 °C

Cable/line

Cable length	1 m
Signal type/category	Sercos CAT5, 100 Mbps
Outer sheath, material	PVC
External sheath, color	signal red RAL 3020
Material, inner sheath	PVC

NBC-MRD/ 1,0-93K/FSD SCO - Network cable



1026097

<https://www.phoenixcontact.com/us/products/1026097>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

UNSPSC

UNSPSC 21.0	26121604
-------------	----------

1026097

<https://www.phoenixcontact.com/us/products/1026097>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com