

TML (EX6)RL - Marker strip

1026829

<https://www.phoenixcontact.com/us/products/1026829>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker strip, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 1, roll length: 150 m, text field height: 6 mm, text field width: 150000 mm

Your advantages

- The self-adhesive marker strips from the SK marking range mark products without a marker groove, ideal for marking COMBICON connectors
- Zack marker strips and flat zack marker strips can be marked subsequently with the TML marking foil
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The thermal transfer printer cutting units make it possible to trim precisely to the required length
- Labeling service: Phoenix Contact can custom-label all TML ... markers in accordance with your requirements

Commercial data

Item number	1026829
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG11
Product key	BG2111
GTIN	4055626519883
Weight per piece (including packing)	416.2 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	49119900
Country of origin	DE

TML (EX6)RL - Marker strip



1026829

<https://www.phoenixcontact.com/us/products/1026829>

Technical data

Notes

General	For the THERMOMARK ROLL and THERMOMARK ROLL 2.0 roll printers, this material can only be processed with an external media hub.
---------	--

Product properties

Product type	Terminal marker
--------------	-----------------

Marking

Number of individual labels	1
Number of individual labels per row	1
Slot type	flat
Identification technology	Thermotransfer

Dimensions

Length of roll	150.00 m
Height	6.00 mm
Depth	0.07 mm

Text field

Text field width	150000 mm
Text field height	6 mm

Material specifications

Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

TML (EX6)RL - Marker strip

1026829

<https://www.phoenixcontact.com/us/products/1026829>



Standards and regulations

Wipe resistance

DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type

adhesive

TML (EX6)RL - Marker strip

1026829

<https://www.phoenixcontact.com/us/products/1026829>



Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

TML (EX6)RL - Marker strip

1026829

<https://www.phoenixcontact.com/us/products/1026829>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com