

# FOC-I-D1PGN-S/LCGCSM - FO coupling



1041780

<https://www.phoenixcontact.com/us/products/1041780>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO coupling, design: LC, degree of protection: IP20, number of positions: 2, material: Plastic, connection method: Coupling, cable outlet: straight

## Product description

LC-duplex coupling, single mode APC, suitable for single mode and multimode applications, integrated self-closing metal laser protection flaps, guide sleeve made of zirconia (ceramic)

## Your advantages

- High reliability with comprehensive quality assurance measures
- Optimized precision (stability) with the use of ceramic sleeves
- Future-proof, thanks to RoHS 2 conformity
- Tailored for compatibility with the DIN rail adapters
- Assembly without special tools

## Commercial data

Item number	1041780
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIDA
GTIN	4055626599922
Weight per piece (including packing)	7.5 g
Weight per piece (excluding packing)	7.4 g
Customs tariff number	85367000
Country of origin	CN

## Technical data

### Notes

Notes on operation	For integration into DIN rail adapter NBC-PP-G1PGY
--------------------	----------------------------------------------------

### Product properties

Product type	Data plug
Type	LC
Number of positions	2
Connection profile	LC
No. of cable outlets	2
Number of slots	2
Protective cover	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated surge voltage	0.8 kV
Nominal current $I_N$	0.5 A
Transmission medium	FO

### Connection data

Connection method	Coupling
-------------------	----------

### Material specifications

Color of the housing part	green
Flammability rating according to UL 94	V0
Ferrule material	Zirconia ceramics
Housing material	Plastic

### Cable/line

Cable type	Fiberglass
External sheath, color	silver-colored
Tensile strength short-term/long-term	40 N
Resistance to oil	no

### FO cable

Number of fibers	2
Attenuation	≤ 0.2 dB

### Mechanical properties

Tensile strength short-term/long-term	40 N
---------------------------------------	------

# FOC-I-D1PGN-S/LCGCSM - FO coupling



1041780

<https://www.phoenixcontact.com/us/products/1041780>

## Mechanical data

Insertion/withdrawal cycles	≥ 500
Extraction force per signal contact	≥ 70 N

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-10 °C ... 70 °C
Resistance to UV radiation	no
Resistance to oil	no

## Standards and regulations

Resistance to oil	no
-------------------	----

## Mounting

Mounting type	Snap in
---------------	---------

# FOC-I-D1PGN-S/LCGCSM - FO coupling



1041780

<https://www.phoenixcontact.com/us/products/1041780>

## Classifications

### ECLASS

ECLASS-13.0	19170116
ECLASS-15.0	19170116

### ETIM

ETIM 10.0	EC000752
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1041780

<https://www.phoenixcontact.com/us/products/1041780>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	2.111 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)