

# UBAL 95 BK - High-current terminal block



1086478

<https://www.phoenixcontact.com/us/products/1086478>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current terminal block, nom. voltage: 1000 V, nominal current: 220 A, number of connections: 2, number of positions: 1, connection method: Screw connection, Rated cross section: 95 mm<sup>2</sup>, cross section: 16 mm<sup>2</sup> - 95 mm<sup>2</sup>, Rated cross section: 95 mm<sup>2</sup>, cross section: 16 mm<sup>2</sup> - 95 mm<sup>2</sup>, mounting type: NS 35/15, NS 35/7,5, color: black

## Your advantages

- Maintenance-free terminal points that are greased beforehand simplify the connection of aluminum conductors
- Tailor-made screw connection for multi-stranded aluminum conductors and copper wires
- Extremely robust housing made from fiberglass-reinforced polyamide with V0 approval
- The special design of the UBAL enables the simultaneous connection of aluminum and copper conductors in various connections

## Commercial data

Item number	1086478
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE13
Product key	BE1311
GTIN	4055626876597
Weight per piece (including packing)	97.2 g
Weight per piece (excluding packing)	97.07 g
Customs tariff number	85369010
Country of origin	EE

# UBAL 95 BK - High-current terminal block



1086478

<https://www.phoenixcontact.com/us/products/1086478>

## Technical data

### Notes

General	Terminal block for aluminum and copper conductors (AL-CU)
---------	---

### General

Note	We recommend using ferrules when using flexible conductor.
------	--

### Product properties

Product type	Feed-through terminal block
Product family	UBAL
Number of positions	1
Number of connections	2
Number of rows	1
Potentials	1

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	7.54 W

### Connection data

Nominal cross section	95 mm <sup>2</sup>
-----------------------	--------------------

### Aluminum conductor

Connection method	Screw connection
Screw thread	M14
Note	Screws with hexagonal socket The following values apply to aluminum conductors The values for aluminum conductors relate to rigid and multi-stranded conductors in accordance with EN 60228. Application notes on connecting aluminum conductors can be found in the download area.
Tightening torque	20 Nm
Stripping length	27 mm
Connection in acc. with standard	IEC 61238-1
Conductor cross-section rigid	16 mm <sup>2</sup> ... 95 mm <sup>2</sup>
Cross section AWG	4 ... 4/0 (converted acc. to IEC)
Nominal cross section	95 mm <sup>2</sup>
Nominal current	220 A
Maximum load current	220 A (with 95 mm <sup>2</sup> conductor cross-section – test current in accordance with IEC 61238-1)
Nominal voltage	1000 V

# UBAL 95 BK - High-current terminal block



1086478

<https://www.phoenixcontact.com/us/products/1086478>

## Copper conductor

Note	The following values apply to copper wires Flexible conductors, class 5, in accordance with EN 60228.
Tightening torque	20 Nm
Stripping length	27 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	16 mm <sup>2</sup> ... 95 mm <sup>2</sup>
Cross section AWG	4 ... 4/0 (converted acc. to IEC)
Conductor cross-section flexible	50 mm <sup>2</sup> ... 70 mm <sup>2</sup>
Conductor cross-section flexible (ferrule without plastic sleeve)	16 mm <sup>2</sup> ... 70 mm <sup>2</sup>
Flexible conductor cross-section (ferrule with plastic sleeve)	16 mm <sup>2</sup> ... 70 mm <sup>2</sup>
2 conductors with same cross section, flexible	16 mm <sup>2</sup> ... 35 mm <sup>2</sup>
Nominal cross section	95 mm <sup>2</sup>
Nominal current	232 A
Maximum load current	232 A (with 95 mm <sup>2</sup> conductor cross-section)
Nominal voltage	1000 V

## Dimensions

Width	25.1 mm
Height	93.6 mm
Depth	58 mm
Depth on NS 35/7,5	58 mm
Depth on NS 35/15	65.5 mm
Hole diameter	2.75 mm

## Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Insulating material group	II
Insulating material	PA
Relative insulation material temperature index (Elec., UL 746 B)	400 °C

## Electrical tests

### Surge voltage test

Test voltage setpoint	8 kV
Result	Test passed

### Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 95 mm <sup>2</sup>	11.4 kA
Result	Test passed

### Power-frequency withstand voltage

# UBAL 95 BK - High-current terminal block



1086478

<https://www.phoenixcontact.com/us/products/1086478>

Test voltage setpoint	2.2 kV
Result	Test passed

## Mechanical properties

### Mechanical data

Open side panel	No
-----------------	----

## Mechanical tests

### Mechanical strength

Result	Test passed
--------	-------------

### Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	15 N
Result	Test passed

### Test for conductor damage and slacking

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	16 mm <sup>2</sup> / 2.9 kg 95 mm <sup>2</sup> /14 kg
Result	Test passed

## Environmental and real-life conditions

### Needle-flame test

Time of exposure	10 s
Result	Test passed

### Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2018-05
Spectrum	Long life test category 2, bogie-mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz
Acceleration	3.12g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

### Shocks

Pulse shape	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

# UBAL 95 BK - High-current terminal block



1086478

<https://www.phoenixcontact.com/us/products/1086478>

## Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

## Standards and regulations

Connection in acc. with standard	IEC 61238-1
	IEC 60947-7-1

## Mounting

Mounting type	NS 35/15
	NS 35/7,5

# UBAL 95 BK - High-current terminal block

1086478

<https://www.phoenixcontact.com/us/products/1086478>



## Drawings

### Circuit diagram



# UBAL 95 BK - High-current terminal block



1086478

<https://www.phoenixcontact.com/us/products/1086478>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1086478>



**EAC**

Approval ID: KZ7500651131219505



**UL Recognized**

Approval ID: FILE E 60425

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
E				
	1000 V	230 A	4 - 4/0	-
Al conductors	1000 V	180 A	4 - 4/0	-

# UBAL 95 BK - High-current terminal block



1086478

<https://www.phoenixcontact.com/us/products/1086478>

## Classifications

### ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

### ETIM

ETIM 10.0	EC000897
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UBAL 95 BK - High-current terminal block



1086478

<https://www.phoenixcontact.com/us/products/1086478>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	1.194 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)