

# PTFIX 1,5-NS35 - DIN rail adapter



1049497

<https://www.phoenixcontact.com/us/products/1049497>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail adapter, for NS 35 and NS 15 for accommodating 1.5 mm<sup>2</sup> FIX blocks in vertical direction, color: gray



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1049497       |
| Packing unit                         | 30 pc         |
| Minimum order quantity               | 30 pc         |
| Sales key                            | BE09          |
| Product key                          | BEAZ11        |
| GTIN                                 | 4055626661513 |
| Weight per piece (including packing) | 3.733 g       |
| Weight per piece (excluding packing) | 3.597 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | PL            |

# PTFIX 1,5-NS35 - DIN rail adapter



1049497

<https://www.phoenixcontact.com/us/products/1049497>

## Technical data

### Notes

|               |  |
|---------------|--|
| Assembly note | for NS 35 and NS 15 for accommodating 1.5 mm <sup>2</sup> FIX blocks in the vertical direction |
|---------------|--|

### Product properties

|              |                   |
|--------------|-------------------|
| Product type | Mounting material |
|--------------|-------------------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 21.6 mm |
| Height | 58.1 mm |
| Depth  | 11 mm   |

### Material specifications

|  |    |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

### Environmental and real-life conditions

#### Ambient conditions

|  |   |
|--|---|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

# PTFIX 1,5-NS35 - DIN rail adapter



1049497

<https://www.phoenixcontact.com/us/products/1049497>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27370419 |
| ECLASS-15.0 | 27370419 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001024 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PTFIX 1,5-NS35 - DIN rail adapter



1049497

<https://www.phoenixcontact.com/us/products/1049497>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.027 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)