

CRIMPFOX-P CK 1.6 ER 2.5 OIC-L - Crimping pliers



1069228

<https://www.phoenixcontact.com/us/products/1069228>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for rolled contacts CK 1,6-ER... OIC, cross section: 0.14 ... 2.5 mm². Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. positioning tool

Your advantages

- The integrated positioning tool ensures that the contacts are perfectly aligned
- Precision-manufactured dies ensure consistently high levels of quality during contact processing
- Parallel motion sequences of the dies for symmetrical and optimum crimping results
- High crimping force with low manual force
- Marked die stations for precise processing of corresponding cross sections

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1069228 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3136 |
| GTIN | 4055626743936 |
| Weight per piece (including packing) | 497.5 g |
| Weight per piece (excluding packing) | 497.5 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

CRIMPFOX-P CK 1.6 ER 2.5 OIC-L - Crimping pliers



1069228

<https://www.phoenixcontact.com/us/products/1069228>

Technical data

Product properties

| | |
|------------------|-----------------------------------|
| Product type | Crimping tool |
| Compression | B crimp |
| Product property | Precise and parallel die guidance |
| | Compact design |
| | Tool-free crimp height setting |
| | Unlockable pressure lock |
| | Fastening lug for safety tape |

Crimping position 1

| | |
|--------------------|----------------------|
| Min. cross section | 0.75 mm ² |
| Max. cross section | 1 mm ² |
| AWG max | 18 |

Crimping position 2

| | |
|--------------------|---------------------|
| Max. cross section | 2.5 mm ² |
| AWG max | 14 |

Crimping position 3

| | |
|--------------------|---------------------|
| Max. cross section | 1.5 mm ² |
| AWG max | 16 |

Crimping position 4

| | |
|--------------------|----------------------|
| Min. cross section | 0.34 mm ² |
| Max. cross section | 0.5 mm ² |
| AWG min | 22 |
| AWG max | 20 |

Connection data

Conductor connection

| | |
|-----------------------------|--|
| Cross section range, metric | 0.34 mm ² ... 2.5 mm ² |
| Cross section range AWG | 22 ... 14 |

Dimensions

| | |
|--------|--------|
| Length | 233 mm |
|--------|--------|

CRIMPFOX-P CK 1.6 ER 2.5 OIC-L - Crimping pliers



1069228

<https://www.phoenixcontact.com/us/products/1069228>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX-P CK 1.6 ER 2.5 OIC-L - Crimping pliers



1069228

<https://www.phoenixcontact.com/us/products/1069228>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com