

TESTFOX M - Multimeter



1212208

<https://www.phoenixcontact.com/us/products/1212208>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Digital multimeter, for DC and AC voltage measurements, feed-through measurements, and resistance measurements

Your advantages

- Phase voltages can be detected precisely thanks to the audible and red light signals
- Cable breaks and faulty lamps in exposed cables can be traced from the phase feed side right to the point of interruption
- Suitable for measuring AC voltages and resistance as well as testing continuity and diodes
- Independently tested and approved according to applicable IEC/EN 61010 standards by the certification institute
- The devices can be used for voltages of up to 600 V category III or 1000 V category II
- They provide professional service engineers and operating engineers with a higher level of protection, thereby ensuring maximum safety during work
- Digital multimeters offer remarkable technology and impressive quality
- The devices are extremely versatile

Commercial data

Item number	1212208
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BH31
Product key	BH3322
GTIN	4046356449793
Weight per piece (including packing)	590.4 g
Weight per piece (excluding packing)	553.6 g
Customs tariff number	90303100
Country of origin	TW

TESTFOX M - Multimeter

1212208

<https://www.phoenixcontact.com/us/products/1212208>



Technical data

Product properties

Product type	Measuring tools
Display scope	2000 digits

Electrical properties

Measuring category	CAT III 600 V / CAT II 1000 V
Power supply	2 x micro battery 1.5 V, LR03, AAA

Material specifications

Color	black
-------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
----------------------	------

Standards and regulations

Tests	IEC/EN 61010-1, DIN VDE 0411
-------	------------------------------

TESTFOX M - Multimeter



1212208

<https://www.phoenixcontact.com/us/products/1212208>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com