

CRIMPFOX 16R TWIN - Crimping pliers



1212845

<https://www.phoenixcontact.com/us/products/1212845>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for TWIN ferrules according to UL 486F, three marked die stations, unlockable pressure lock, lateral entry

Your advantages

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25 %

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212845 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3131 |
| GTIN | 4055626406220 |
| Weight per piece (including packing) | 689.6 g |
| Weight per piece (excluding packing) | 689.6 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

CRIMPFOX 16R TWIN - Crimping pliers



1212845

<https://www.phoenixcontact.com/us/products/1212845>

Technical data

Notes

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Product properties

| | |
|--------------------|---------------------------------|
| Product type | Crimping tool |
| Compression | WM crimp |
| Product property | Low grip span |
| | Up to 25% lower actuation force |
| | Suitable for TWIN ferrules |
| Max. cross section | 6 mm ² |
| Max. cross section | 10 mm ² |
| Max. cross section | 16 mm ² |

Connection data

Conductor connection

| | |
|-----------------------------|--|
| Cross section range, metric | 6 mm ² ... 16 mm ² (2 x 6 mm ² ... 2 x 16 mm ²) |
| Cross section range AWG | 10 ... 6 (2 x AWG 10 ... 2 x AWG 6) |

Dimensions

| | |
|--------|--------|
| Width | 25 mm |
| Height | 68 mm |
| Length | 256 mm |

Material specifications

| | |
|-------|-------|
| Color | black |
|-------|-------|

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 6 mm ... 8.5 mm |
|-------------------------|-----------------|

CRIMPFOX 16R TWIN - Crimping pliers



1212845

<https://www.phoenixcontact.com/us/products/1212845>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212845>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 16R TWIN - Crimping pliers



1212845

<https://www.phoenixcontact.com/us/products/1212845>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX 16R TWIN - Crimping pliers



1212845

<https://www.phoenixcontact.com/us/products/1212845>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com