

# USA 10 BK - Rail adapter

1200993

<https://www.phoenixcontact.com/us/products/1200993>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Rail adapter, for M3 screws, depth: 7.3 mm, width: 10 mm, height: 42.6 mm, diameter: 2.8 mm, color: black



## Commercial data

Item number	1200993
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE07
Product key	BE7114
GTIN	4017918255879
Weight per piece (including packing)	2.86 g
Weight per piece (excluding packing)	2.86 g
Customs tariff number	39269097
Country of origin	DE

# USA 10 BK - Rail adapter

1200993

<https://www.phoenixcontact.com/us/products/1200993>



## Technical data

### Product properties

Product type	Mounting material
--------------	-------------------

### Dimensions

Width	10 mm
Height	42.6 mm
Depth	7.3 mm
Diameter	2.8 mm

### Material specifications

Color	black (RAL 9005)
Material	PA
Flammability rating according to UL 94	V2
Coating	uncoated

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# USA 10 BK - Rail adapter

1200993

<https://www.phoenixcontact.com/us/products/1200993>



## Classifications

### ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

### ETIM

ETIM 10.0	EC002848
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# USA 10 BK - Rail adapter

1200993

<https://www.phoenixcontact.com/us/products/1200993>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.019 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)