

# SAC-3P-M12MS/1,5-PUR/B-1L-Z - Sensor/actuator cable



1400778

<https://www.phoenixcontact.com/us/products/1400778>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, with 1 LED, on Valve connector B (10 mm), with 1 LED, Wiring: Z diode, cable length: 1.5 m

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1400778       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF07          |
| Product key                          | AF1DLA        |
| GTIN                                 | 4046356511551 |
| Weight per piece (including packing) | 76.1 g        |
| Weight per piece (excluding packing) | 71.7 g        |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# SAC-3P-M12MS/1,5-PUR/B-1L-Z - Sensor/actuator cable



1400778

<https://www.phoenixcontact.com/us/products/1400778>

## Technical data

### Product properties

|                      |  |
|----------------------|--|
| Product type         | Sensor/actuator cable with valve connector |
| Number of positions  | 3  |
| No. of cable outlets | 1  |
| Shielded             | no   |
| Coding               | A  |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Material specifications

|  |                              |
|--|------------------------------|
| Flammability rating according to UL 94 | HB                           |
| Seal material                          | TPU                          |
| Material housing valve plug            | TPU                          |
| Material of grip body                  | TPU                          |
| Contact material                       | CuSn                         |
| Contact surface material               | Ni/Au                        |
| Contact carrier material               | TPU GF                       |
| Contact material                       | CuSn                         |
| Valve plug contact insert material     | PA 6.6                       |
| Contact surface material               | Sn                           |
| Material for screw connection          | Zinc die-cast, nickel-plated |

### Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 24 V AC |
|                       | 24 V DC |
| Nominal current $I_N$ | 4 A     |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |       |
|------------------------|-------|
| Status display         | 1 LED |
| Status display present | yes   |

### Connector

#### Connection 1

|                     |                   |
|---------------------|-------------------|
| Type                | Plug straight M12 |
| Number of positions | 3                 |

# SAC-3P-M12MS/1,5-PUR/B-1L-Z - Sensor/actuator cable

1400778

<https://www.phoenixcontact.com/us/products/1400778>

|             |   |
|-------------|---|
| Coding type | A |
|-------------|---|


## Connection 2

|                     |                           |
|---------------------|---------------------------|
| Type                | Valve connector B (10 mm) |
| Number of positions | 3                         |
| Material            | CuSn (Contact)            |
|                     | Sn (Contact surface)      |
|                     | PA 6.6 (Contact carrier)  |
|                     | TPU (Housing)             |
| Protective circuit  | Z diode                   |

## Cable/line

|              |       |
|--------------|-------|
| Cable length | 1.5 m |
|--------------|-------|

## PUR halogen-free black [PUR]

|   |   |
|---|---|
| Dimensional drawing                           |  |
| Cable weight                                  | 30 kg/km  |
| UL AWM Style                                  | 20549   |
| Number of positions                           | 3   |
| Shielded                                      | no  |
| Cable type                                    | PUR halogen-free black [PUR]  |
| Conductor structure signal line               | 28x 0.15 mm   |
| AWG signal line                               | 20  |
| Conductor cross-section                       | 3x 0.5 mm <sup>2</sup>  |
| Wire diameter incl. insulation                | 1.5 mm ±0.05 mm (Signal line)   |
| External cable diameter                       | 4.50 mm ±0.2 mm   |
| Outer sheath, material                        | PUR   |
| External sheath, color                        | black-gray RAL 7021   |
| Conductor material                            | Bare Cu litz wires  |
| Material wire insulation                      | PP  |
| Single wire, color                            | black 1, black 2, green/yellow  |
| Overall twist                                 | 3 wires, twisted  |
| Max. conductor resistance                     | 39 Ω/km (at 20 °C)  |
| Insulation resistance                         | min. 20 MΩ*km   |
| Nominal voltage, cable                        | ≤ 300 V   |
| Test voltage                                  | ≥ 1200 V  |
| Minimum bending radius, fixed installation    | 5 x D   |
| Minimum bending radius, flexible installation | 10 x D  |

# SAC-3P-M12MS/1,5-PUR/B-1L-Z - Sensor/actuator cable



1400778

<https://www.phoenixcontact.com/us/products/1400778>

|   |   |
|---|---|
| Smallest bending radius, fixed installation   | 22.5 mm   |
| Smallest bending radius, movable installation | 45 mm   |
| Dynamic load capacity (bending)               | Max. bending cycles: 15000000, Bending radius: 50 mm, Traversing path: 0.9 m, Traversing rate: 5 m/s, Acceleration: 30 m/s <sup>2</sup> |
| Halogen-free                                  | in accordance with DIN VDE 0472 part 815  |
| Flame resistance                              | according to DIN VDE 0482<br>According to DIN EN 50265-2-1  |
| Resistance to oil                             | in accordance with DIN EN 60811-2-1   |
| Other resistance                              | largely oil-resistant<br>partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)   |
| Ambient temperature (operation)               | -40 °C ... 80 °C (cable, fixed installation)<br>-20 °C ... 80 °C (Cable, flexible installation)   |

## Environmental and real-life conditions

### Ambient conditions

|   |                                    |
|---|------------------------------------|
| Degree of protection  | IP65<br>IP67                       |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket)   |
| Ambient temperature (operation) (Valve connector)                 | -20 °C ... 85 °C (Valve connector) |

## Standards and regulations

|                      |                 |
|----------------------|-----------------|
| Standard designation | Valve connector |
|----------------------|-----------------|

# SAC-3P-M12MS/1,5-PUR/B-1L-Z - Sensor/actuator cable



1400778

<https://www.phoenixcontact.com/us/products/1400778>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1400778>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387



**CSAus**

Approval ID: 13631

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 24 V                  | 4 A                   | -                 | -                           |

# SAC-3P-M12MS/1,5-PUR/B-1L-Z - Sensor/actuator cable



1400778

<https://www.phoenixcontact.com/us/products/1400778>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060312 |
| ECLASS-15.0 | 27060312 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

# SAC-3P-M12MS/1,5-PUR/B-1L-Z - Sensor/actuator cable



1400778

<https://www.phoenixcontact.com/us/products/1400778>

## Environmental product compliance

### EU RoHS

|   |        |
|---|--------|
| Fulfills EU RoHS substance requirements | Yes    |
| Exemption                               | 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |  |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Diboron trioxide(CAS: 1303-86-2)           |
|                                     | Lead monoxide (lead oxide)(CAS: 1317-36-8) |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)