

# SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/us/products/1401690>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Master cable ring, application: Distributor boxes, number of positions: 11, cable length: 50 m



## Commercial data

Item number	1401690
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF45
Product key	AF3ZBX
GTIN	4046356569521
Weight per piece (including packing)	5,945 g
Weight per piece (excluding packing)	5,945 g
Customs tariff number	85444995
Country of origin	DE

# SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring

1401690

<https://www.phoenixcontact.com/us/products/1401690>

## Technical data

### Product properties

Product type	Cable by the meter
Application	Distributor boxes
Number of positions	11


### Electrical properties

Nominal voltage $U_N$	300 V AC
	300 V DC

### Cable/line

Cable length	50 m
--------------	------

### PUR halogen-free black [PUR]

Dimensional drawing	
Number of positions	11
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	64x 0.10 mm
AWG signal line	20
Conductor structure, voltage supply	128x 0.10 mm
AWG power supply	17
Conductor cross-section	3x 1 mm <sup>2</sup> (power line) 8x 0.5 mm <sup>2</sup> (Signal line)
External cable diameter	9.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, green/yellow, white, green, yellow, gray, gray/pink, red/blue, white/green, brown/green
Overall twist	Wires twisted in layers
Nominal voltage, cable	300 V
Test voltage	2000 V
Smallest bending radius, fixed installation	94 mm
Smallest bending radius, movable installation	94 mm

# SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/us/products/1401690>

Dynamic load capacity (bending)	Max. bending cycles: 1500000, Bending radius: 94 mm, Traversing path: 2 m, Traversing rate: 2 m/s
Flame resistance	DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803
Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

# SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/us/products/1401690>

## Classifications

### ECLASS

ECLASS-13.0	27060106
ECLASS-15.0	27060106

### ETIM

ETIM 10.0	EC003250
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SACB-8X0,5/3X1,0-50,0 HPUR - Master cable ring



1401690

<https://www.phoenixcontact.com/us/products/1401690>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)