

VS-PPC-C1-MNNA-4Q5-EMC - RJ45 connector



1403366

<https://www.phoenixcontact.com/us/products/1403366>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Push/pull EMC connector

RJ45 connector, degree of protection: IP65/IP67, number of positions: 4, CAT5 (IEC 11801:2002), material: Metal, connection method: IDC fast connection, connection cross section: AWG 22- 22, cable outlet: straight, color: silver, PROFINET

Commercial data

Item number	1403366
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOAA
GTIN	4046356708319
Weight per piece (including packing)	79.6 g
Weight per piece (excluding packing)	79.6 g
Customs tariff number	85366990
Country of origin	DE

1403366

<https://www.phoenixcontact.com/us/products/1403366>

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Number of positions	4
Connection profile	RJ45 8(4)
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Nominal voltage U_N	48 V
Nominal current I_N	1.75 A
Contact resistance	0.001 Ω (Wire – IDC)
	0.005 Ω (Litz wires – IDC)
Transmission medium	Copper
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

Connection data

Connection technology

Connection method	IDC fast connection
Connection cross section AWG	22 ... 22 (solid)
	22 ... 22 (flexible)
Conductor cross-section	0.32 mm ² (solid)
	0.36 mm ² (flexible)

Interfaces

Signal type/category	PROFINET CAT5 (IEC 11801:2002)
----------------------	--------------------------------

Dimensions

Width	22 mm
Height	30 mm
Length	72 mm

Material specifications

Color	silver
-------	--------

VS-PPC-C1-MNNA-4Q5-EMC - RJ45 connector



1403366

<https://www.phoenixcontact.com/us/products/1403366>

Material	Metal
Flammability rating according to UL 94	V0
Seal material, O-ring	NBR
Seal material cable seal	TPE
Seal material	NBR
Housing material	Metal
Housing surface material	nickel-plated
Cable seal material	TPE
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
O-ring material	NBR
Material for screw connection	CuZn

Cable/line

Signal type/category	PROFINET CAT5 (IEC 11801:2002)
External cable diameter	5 mm ... 8 mm
External cable diameter	5 mm ... 8 mm
Cable cross section	0.14 mm ²

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Ambient temperature (assembly)	-5 °C ... 45 °C

Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

VS-PPC-C1-MNNA-4Q5-EMC - RJ45 connector



1403366

<https://www.phoenixcontact.com/us/products/1403366>

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC002636
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1403366

<https://www.phoenixcontact.com/us/products/1403366>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
	2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	4c36334a-a348-4c03-908d-385a8733c65d

EF3.1 Climate Change

CO2e kg	1.785 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com