

# SAC-3P-M5MS/0,8-PUR/M5FS - Sensor/actuator cable



1402495

<https://www.phoenixcontact.com/us/products/1402495>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR, black RAL 9005, Plug straight M5, coding: A, on Socket straight M5, coding: A, cable length: 0.8 m

## Commercial data

Item number	1402495
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	B06
Product key	AF1ABA
GTIN	4046356620338
Weight per piece (including packing)	21.8 g
Weight per piece (excluding packing)	21.8 g
Customs tariff number	85444290
Country of origin	DE

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Material of grip body	PUR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PUR
Material for screw connection	Brass, nickel-plated
Outer sheath, material	PUR

### Electrical properties

Insulation resistance	$\geq 10 \text{ G}\Omega$
Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	1 A

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	$\geq 100$
-----------------------------	------------

### Signaling

Status display	no
Status display present	no

### Connector

#### Connection 1

Type	Plug straight M5
Number of positions	3
Coding type	A

#### Connection 2

Type	Socket straight M5
Number of positions	3

# SAC-3P-M5MS/0,8-PUR/M5FS - Sensor/actuator cable



1402495


<https://www.phoenixcontact.com/us/products/1402495>

Coding type	A
-------------	---

## Cable/line

Cable length	0.8 m
--------------	-------

PUR/PVC black [350]

Dimensional drawing	
Cable weight	12.9 kg/km
Number of positions	3
Shielded	no
Cable type	PUR/PVC black [350]
Conductor structure signal line	18x 0.10 mm
AWG signal line	26
Conductor cross-section	3x 0.14 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.1 mm
External cable diameter	3.00 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Overall twist	3 wires, twisted
Max. conductor resistance	148 Ω/km
Insulation resistance	100 MΩ*km
Nominal voltage, cable	250 V
Test voltage	800 V <sub>rms</sub>
Smallest bending radius, fixed installation	8 mm
Smallest bending radius, movable installation	15 mm
Ambient temperature (operation)	-15 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)


## Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 80 °C (Plug / socket)


## Drawings

Dimensional drawing




Plug M5 x 0.5, straight

Dimensional drawing




Socket M5 x 0.5, straight

Schematic diagram




Plug M5, 3-pos.

Schematic diagram



Socket M5, 3-pos.

Circuit diagram



Contact assignment of the M5 male/female connectors

# SAC-3P-M5MS/0,8-PUR/M5FS - Sensor/actuator cable



1402495

<https://www.phoenixcontact.com/us/products/1402495>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

1402495

<https://www.phoenixcontact.com/us/products/1402495>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)