


VS-ASI-FC-PUR-YE/1000 - Flat cable



1404841

<https://www.phoenixcontact.com/us/products/1404841>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



AS-Interface PUR flat-ribbon conductor in yellow, 2 x 1.5 mm², 1000 m on a disposable drum

Commercial data

Item number	1404841
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LFA
GTIN	4046356327572
Weight per piece (including packing)	222.22 g
Weight per piece (excluding packing)	222.22 g
Customs tariff number	85444995
Country of origin	DE

1404841

<https://www.phoenixcontact.com/us/products/1404841>

Technical data

Product properties

Product type	Data cable by the meter
Sensor type	AS-Interface
Number of positions	2
Shielded	no

Electrical properties

Rated voltage (III/3)	32 V
Rated surge voltage	2 kV

Interfaces

Signal type/category	AS-Interface
----------------------	--------------

Dimensions

Width	10 mm
Height	4 mm

Cable/line

Cable length	1000 m
Cable weight	64 kg/km
Number of positions	2
Shielded	no
Conductor structure	2 x 1.5 mm ²
Conductor type	Flat cable
Conductor structure signal line	84x 0.15 mm
AWG signal line	16
Conductor cross-section	1.5 mm ²
Wire diameter incl. insulation	2.5 mm
Outer sheath, material	PUR
External sheath, color	lemon yellow RAL 1012
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue
Thickness, insulation	approx. 0.50 mm
Max. conductor resistance	≤ 13.7 Ω/km
Insulation resistance	≥ 1 MΩ*km
Nominal voltage, cable	32 V
Test voltage	2000 V
Smallest bending radius, fixed installation	≥ 6 mm (one-time)
Dynamic load capacity (bending)	Max. bending cycles: 8000000, Bending radius: 75 mm, Traversing direction: horizontal, above the broadside, Traversing rate: 4 m/s, Acceleration: 4 m/s ²

VS-ASI-FC-PUR-YE/1000 - Flat cable



1404841

<https://www.phoenixcontact.com/us/products/1404841>

	Max. bending cycles: 10000000, Bending radius: 50 mm, Traversing direction: vertical, above the broadside
Halogen-free	yes
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 85 °C (cable, fixed installation) -30 °C ... 85 °C (Cable, flexible installation)

FO cable

Transmission medium	Copper
---------------------	--------

Mechanical properties

Duty cycle testing	suitable for drag chain
--------------------	-------------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (fixed routing) -30 °C ... 85 °C (Flexibly installed)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-30 °C ... 85 °C

Standards and regulations

Testing

Duty cycle testing	suitable for drag chain
--------------------	-------------------------

VS-ASI-FC-PUR-YE/1000 - Flat cable



1404841

<https://www.phoenixcontact.com/us/products/1404841>

Classifications

UNSPSC

UNSPSC 21.0	26121707
-------------	----------

VS-ASI-FC-PUR-YE/1000 - Flat cable



1404841

<https://www.phoenixcontact.com/us/products/1404841>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com