

SACC-DSI-FS-12P-PG9-L180 SCOGN - Device connector rear mounting



1405328

<https://www.phoenixcontact.com/us/products/1405328>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 12-position, Socket, M12-SPEEDCON, A-coding, Wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1405328
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB26
Product key	ABQEHL
GTIN	4046356746458
Weight per piece (including packing)	14.645 g
Weight per piece (excluding packing)	13.503 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-FS-12P-PG9-L180 SCOGN - Device connector rear mounting



1405328

<https://www.phoenixcontact.com/us/products/1405328>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Mounting

Mounting type	Rear mounting (Pg9)
Tightening torque	2 Nm ... 3 Nm

Product properties

Product type	Circular connectors (device side)
Application	Signal
Number of positions	12
Coding	A
Thread type	M12

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Socket
Tightening torque	2 Nm ... 3 Nm

Connector

Connection 1

Head design	Socket
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Environmental and real-life conditions

Ambient conditions

UL Type Rating	Type 4 (indoor use only)
----------------	--------------------------


SACC-DSI-FS-12P-PG9-L180 SCOGN - Device connector rear mounting

1405328

<https://www.phoenixcontact.com/us/products/1405328>

Drawings

Schematic diagram



Pin assignment M12, 12-pos., female side view

SACC-DSI-FS-12P-PG9-L180 SCOGN - Device connector rear mounting




1405328

<https://www.phoenixcontact.com/us/products/1405328>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405328>

 cULus Recognized Approval ID: E221474-20140616		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		30 V	1.5 A	-	-

SACC-DSI-FS-12P-PG9-L180 SCOGN - Device connector rear mounting



1405328

<https://www.phoenixcontact.com/us/products/1405328>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SACC-DSI-FS-12P-PG9-L180 SCOGN - Device connector rear mounting



1405328

<https://www.phoenixcontact.com/us/products/1405328>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	269db1d5-00ec-4cee-9ff3-68f3ece738c2

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com