

VS-PPC-J-1-SCRJ-MNBK - FO coupling

1405206

<https://www.phoenixcontact.com/us/products/1405206>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

SC-RJ push-pull coupling, IP65, metal, with protective cover, color: nickel-plated



SCRJ push-pull coupling

Commercial data

Item number	1405206
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOBZ
GTIN	4046356332804
Weight per piece (including packing)	113.9 g
Weight per piece (excluding packing)	115.7 g
Customs tariff number	85366990
Country of origin	DE

1405206

<https://www.phoenixcontact.com/us/products/1405206>

Technical data

Product properties

Product type	Female insert
Type	SC-RJ
Sensor type	Ethernet
Number of positions	2
Connection profile	SCRJ
Cable outlet	straight

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated surge voltage	0.8 kV
Attenuation	0.2 dB (acc. to IEC 61300-3-4)
Insulation resistance	≥ 500 MΩ
Nominal current I_N	0.5 A
Transmission medium	FO

Connection data

Connection technology

Connection method	Coupling
-------------------	----------

Dimensions

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Material specifications

Color	silver
Material	Metal
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated

Cable/line

Cable type	Fiber optics
Resistance to oil	yes
Flame resistance	yes

FO cable

Number of fibers	2
Fiber type	GOF, PCF, POF

VS-PPC-J-1-SCRJ-MNBK - FO coupling



1405206

<https://www.phoenixcontact.com/us/products/1405206>

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	>= 500
-----------------------------	--------

Characteristics

Attenuation	0.2 dB (acc. to IEC 61300-3-4)
-------------	--------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	0 °C ... 50 °C
Resistance to oil	yes

Standards and regulations

Flame resistance	yes
Resistance to oil	yes

VS-PPC-J-1-SCRJ-MNBK - FO coupling



1405206

<https://www.phoenixcontact.com/us/products/1405206>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405206>



UL Listed

Approval ID: E308814-20070105

VS-PPC-J-1-SCRJ-MNBK - FO coupling



1405206

<https://www.phoenixcontact.com/us/products/1405206>

Classifications

ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	19170116

ETIM

ETIM 10.0	EC000752
-----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

VS-PPC-J-1-SCRJ-MNBK - FO coupling



1405206

<https://www.phoenixcontact.com/us/products/1405206>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com