

# SAC-8P-6,38-PUR/M12FS D-SBER - Sensor/actuator cable



1405624

<https://www.phoenixcontact.com/us/products/1405624>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-pos., PUR, halogen-free, black-gray RAL 7021, plug, nominal current: 12 A, number of positions: 6, pitch: 5.08 mm, connection method: spring-cage connection, color: green, contact surface material: tin, to straight M12 socket, A-coded, cable length: 6.38 m

## Commercial data

Item number	1405624
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CFA
GTIN	4046356751407
Weight per piece (including packing)	306.1 g
Weight per piece (excluding packing)	306.1 g
Country of origin	PL

# SAC-8P-6,38-PUR/M12FS D-SBER - Sensor/actuator cable



1405624

<https://www.phoenixcontact.com/us/products/1405624>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	8
No. of cable outlets	1
Shielded	no
Coding	A

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	PUR
Conductor material	Bare Cu litz wires

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V AC
	30 V DC
Nominal current $I_N$	2 A
Max. conductor resistance	78 $\Omega/\text{km}$

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	$\geq 100$
-----------------------------	------------

### Signaling

Status display	no
Status display present	no

### Connection data

#### Connection technology

Connection method	Spring-cage connection
-------------------	------------------------

#### Conductor connection

# SAC-8P-6,38-PUR/M12FS D-SBER - Sensor/actuator cable



1405624

<https://www.phoenixcontact.com/us/products/1405624>

Connection method	Spring-cage connection
-------------------	------------------------

## Connector

### Connection 1

Type	free cable end
------	----------------


### Connection 2

Type	Socket straight M12
Number of positions	8
Coding type	A

## Cable/line

Cable length	6.38 m
--------------	--------

### PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	46 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	8
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	8x 0.25 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.02 mm
External cable diameter	5.90 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material, filler	PE
Material wire insulation	PP
Single wire, color	white, brown, green, yellow, gray, pink, blue, red
Thickness, insulation	≥ 0.21 mm
Thickness, outer sheath	approx. 0.80 mm
Overall twist	8 wires around filler to the core
Max. conductor resistance	≤ 78 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)

# SAC-8P-6,38-PUR/M12FS D-SBER - Sensor/actuator cable



1405624

<https://www.phoenixcontact.com/us/products/1405624>

Wave impedance	100 Ω +15 % (with 1 MHz)
Cable capacity	≤ 70 pF/m
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	8 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	48 mm
Smallest bending radius, movable installation	59 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 59 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 According to DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) Low adhesion abrasion-resistant
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish flexible
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

## Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

# SAC-8P-6,38-PUR/M12FS D-SBER - Sensor/actuator cable

1405624

<https://www.phoenixcontact.com/us/products/1405624>

## Drawings

Dimensional drawing



M12 x 1 socket, straight

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

# SAC-8P-6,38-PUR/M12FS D-SBER - Sensor/actuator cable



1405624

<https://www.phoenixcontact.com/us/products/1405624>

Circuit diagram



Contact assignment of the M12 socket

# SAC-8P-6,38-PUR/M12FS D-SBER - Sensor/actuator cable



1405624

<https://www.phoenixcontact.com/us/products/1405624>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)