

# SACCBP-8P-MS/0,5-PUR/M12FSSCO - Connector



1405728

<https://www.phoenixcontact.com/us/products/1405728>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, degree of protection: IP65/IP67

## Commercial data

Item number	1405728
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AB28
Product key	ABQSAH
GTIN	4046356759229
Weight per piece (including packing)	67.4 g
Weight per piece (excluding packing)	67.4 g
Customs tariff number	85444290
Country of origin	DE

# SACCBP-8P-MS/0,5-PUR/M12FSSCO - Connector




1405728

<https://www.phoenixcontact.com/us/products/1405728>

## Technical data

### Cable/line

PUR halogen-free black [PUR]

Dimensional drawing	
Shielded	yes
UL AWM Style	20549 / 10493 (80°C/300 V)
Cable weight	53 kg/km
Cable type	PUR halogen-free black
Cable type (abbreviation)	PUR
External cable diameter	5.90 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Thickness, outer sheath	approx. 0.50 mm
Conductor material	Bare Cu litz wires
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	8x 0.25 mm <sup>2</sup> (Signal line)
Material wire insulation	PP
Thickness, insulation	approx. 0.20 mm
Wire diameter incl. insulation	1.17 mm ±0.02 mm
Single wire, color	brown, white, green, yellow, gray, pink, blue, red
Overall twist	8 wires around filler to the core
Shielding	Tinned copper braided shield
Optical shield covering	85 %
Nominal voltage, cable	≤ 300 V AC
Test voltage Core/Shield	≥ 2000.00 V AC (for 60 s)
Test voltage, cable	≥ 3000 V AC (Spark test)
Cable resistance	≤ 78 Ω/km (at 20 °C)
Cable insulation resistance	≥ 1 GΩ*km (at 20 °C)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Number of bending cycles	10000000
Minimum bending radius, drag chain applications	10 x D
Traversing path	10 m

# SACCBP-8P-MS/0,5-PUR/M12FSSCO - Connector



1405728

<https://www.phoenixcontact.com/us/products/1405728>

Traversing rate	3 m/s
Acceleration	10 m/s <sup>2</sup>
Torsion force	± 180 °/m
Torsion cycles	≥ 5000000
Torsional frequency	35 (cycles/min.)
Halogen-free	in accordance with DIN VDE 0472 part 815 according to IEC 60754-1
Resistance to oil	in accordance with IEC 60811-404
Flame resistance	in acc. with UL FT-2 according to UL 758/1581 (horizontal) in accordance with UL 758/1581 FT2 According to DIN EN 60332-2-2 (20 s)
Other resistance	hydrolysis and microbe resistant Resistant to salt water low-abrasion partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable
Ambient temperature (operation)	-25 °C ... 80 °C (Cable, flexible installation) -40 °C ... 80 °C (cable, fixed installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67

# SACCBP-8P-MS/0,5-PUR/M12FSSCO - Connector



1405728

<https://www.phoenixcontact.com/us/products/1405728>

## Classifications

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1405728

<https://www.phoenixcontact.com/us/products/1405728>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)