

SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable



1406309

<https://www.phoenixcontact.com/us/products/1406309>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, yellow, Plug angled M12, coding: A, on Socket straight M12, cable length: 1.5 m

Commercial data

Item number	1406309
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF13
Product key	AF1ICA
GTIN	4046356797443
Weight per piece (including packing)	64.2 g
Weight per piece (excluding packing)	56.4 g
Customs tariff number	85444290
Country of origin	US

SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable



1406309

<https://www.phoenixcontact.com/us/products/1406309>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard, U.S. cables
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.4 Nm (M12 connector)
-------------------	------------------------

Connector

Connection 1

SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable



1406309

<https://www.phoenixcontact.com/us/products/1406309>

Type	Plug angled M12
Number of positions	3
Coding type	A


Connection 2

Type	Socket straight M12
Number of positions	3

Cable/line

Cable length	1.5 m
--------------	-------

PVC yellow 105 °C [542]

Dimensional drawing	
Cable weight	30 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	3
Shielded	no
Cable type	PVC yellow 105 °C [542]
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Wire diameter incl. insulation	1.27 mm ±0.03 mm
External cable diameter	4.70 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	yellow
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Overall twist	3 wires, twisted
Max. conductor resistance	max. 50.5 Ω/km (20 °C)
Insulation resistance	≥ (550 M Ohms/m @ 500V)
Nominal voltage, cable	300 V
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, movable installation	38 mm
Flame resistance	FT4
Other resistance	UV resistant
Special properties	UL standards PLTC and ITC
Ambient temperature (operation)	-30 °C ... 105 °C (cable, fixed installation) -5 °C ... 105 °C (Cable, flexible installation)

SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable



1406309

<https://www.phoenixcontact.com/us/products/1406309>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable

1406309

<https://www.phoenixcontact.com/us/products/1406309>


Drawings

Dimensional drawing



M12 x 1 male plug, angled

Dimensional drawing




M12 x 1 socket, straight

SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable

1406309


<https://www.phoenixcontact.com/us/products/1406309>

Schematic diagram



Pin assignment M12 plug, 3-pos., A-coded, view male side

Schematic diagram




Pin assignment M12 socket, 3-pos., A-coded, view female side

SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable

1406309

<https://www.phoenixcontact.com/us/products/1406309>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable





1406309

<https://www.phoenixcontact.com/us/products/1406309>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1406309>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	4 A	-	-

 EAC-RoHS Approval ID: RU D-DE.HB35.B.00387	
--	--

SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable



1406309

<https://www.phoenixcontact.com/us/products/1406309>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-MR/ 1,5-542/ FS SCO BK - Sensor/actuator cable



1406309

<https://www.phoenixcontact.com/us/products/1406309>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.437 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com