

HC-D-G-M25-PLRBK - Cable gland

1411351

<https://www.phoenixcontact.com/us/products/1411351>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



EVO plastic cable gland with bayonet locking, for housing series D, size M25, cable diameter: 9 mm ... 17 mm.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1411351 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF57 |
| Product key | AF7APN |
| GTIN | 4046356929226 |
| Weight per piece (including packing) | 33.8 g |
| Weight per piece (excluding packing) | 32 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

HC-D-G-M25-PLRBK - Cable gland

1411351

<https://www.phoenixcontact.com/us/products/1411351>

Technical data


Mounting

| | |
|---------------|--|
| Assembly note | Bayonet locking max. 3x can be removed |
|---------------|--|

Product properties

| | |
|------------------------------|-------------------|
| Product type | Cable screw gland |
| No. of conductors | 1 |
| Type of the screw connection | M25 |
| Shielded | no |

Dimensions

| | |
|------------------------|---|
| Dimensional drawing |  |
| Wrench size, union nut | 26 mm |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| Material Pressure screw | PA |
| Flammability rating according to UL 94 | V0 / V2 |
| Seal material O-ring | NBR |
| Seal material Cable seal | NBR |
| Material for screw connection | PA |

Cable/line

| | |
|---------------------------------|----------------|
| External cable diameter Cable 1 | 9 mm ... 17 mm |
|---------------------------------|----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP66 |
| Enclosure rating (NEMA) | 12 (UL 50e) |
| Ambient temperature (operation) | -40 °C ... 100 °C |

HC-D-G-M25-PLRBK - Cable gland


1411351

<https://www.phoenixcontact.com/us/products/1411351>



Drawings

Dimensional drawing



Dimensional drawing

HC-D-G-M25-PLRBK - Cable gland



1411351

<https://www.phoenixcontact.com/us/products/1411351>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411351>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026

HC-D-G-M25-PLRBK - Cable gland



1411351

<https://www.phoenixcontact.com/us/products/1411351>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27140801 |
| ECLASS-15.0 | 27140801 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000441 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

HC-D-G-M25-PLRBK - Cable gland



1411351

<https://www.phoenixcontact.com/us/products/1411351>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.301 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com