

HC-EVO-B10-HLFS-EL-AL - Housing



1411456

<https://www.phoenixcontact.com/us/products/1411456>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON EVO sleeve housing, EMC version, without powder coating, with bayonet flange for EVO screw connection, B10, for single locking latch, height: 64 mm, without EVO screw connection.

Your advantages

- Flexible cable outlet direction, lateral or straight

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1411456 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF57 |
| Product key | AF7APM |
| GTIN | 4046356932639 |
| Weight per piece (including packing) | 146 g |
| Weight per piece (excluding packing) | 143.9 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

HC-EVO-B10-HLFS-EL-AL - Housing

1411456


<https://www.phoenixcontact.com/us/products/1411456>

Technical data

Product properties

| | |
|----------------------|----------------------------|
| Product type | Housing with locking latch |
| Housing type | Sleeve housing |
| Application | Standard |
| Type | B10 |
| No. of cable outlets | 1 |
| Cable outlet | straight |
| Pg screw connection | none |

Dimensions

| | |
|---------------------|---|
| Dimensional drawing |  |
| Width | 44 mm |
| Height | 64 mm |
| Length | 73 mm |

Material specifications

| | |
|--------------------------|---|
| Housing material | Die-cast aluminum, salt water resistant |
| Housing surface material | uncoated |

Mechanical properties

Mechanical data

| | |
|--------------|-----|
| Locking type | Pin |
|--------------|-----|

Mounting

| | |
|---------------|--|
| Assembly note | The sleeve base housing must be supplemented with the EVO screw connection. The EVO screw connection is available in 4 sizes. It enables the creation of a straight or a lateral cable outlet. The EVO screw connection is assembled by hand or using a pipe wrench. |
|---------------|--|

Environmental and real-life conditions

Ambient conditions

| | |
|-------------------------|-------------|
| Degree of protection | IP66 |
| | IP67 |
| Enclosure rating (NEMA) | 4 (UL 50e) |
| | 4X (UL 50e) |
| | 12 (UL 50e) |
| Impact strength | IK08 |

HC-EVO-B10-HLFS-EL-AL - Housing



1411456

<https://www.phoenixcontact.com/us/products/1411456>

Ambient temperature (operation)

-40 °C ... 125 °C

HC-EVO-B10-HLFS-EL-AL - Housing




1411456

<https://www.phoenixcontact.com/us/products/1411456>

Drawings

Dimensional drawing



Dimensional drawing

HC-EVO-B10-HLFS-EL-AL - Housing



1411456

<https://www.phoenixcontact.com/us/products/1411456>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411456>

DNV

Approval ID: TAE000037S



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-EVO-B10-HLFS-EL-AL - Housing



1411456

<https://www.phoenixcontact.com/us/products/1411456>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000437 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

HC-EVO-B10-HLFS-EL-AL - Housing



1411456

<https://www.phoenixcontact.com/us/products/1411456>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com