

# SAC-8P-MS/ 1,2-PUR/FS SCO BK - Sensor/actuator cable



1411970

<https://www.phoenixcontact.com/us/products/1411970>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 1.2 m, with black grip

## Commercial data

Item number	1411970
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CFA
GTIN	4046356946858
Weight per piece (including packing)	76 g
Weight per piece (excluding packing)	76 g
Country of origin	PL

# SAC-8P-MS/ 1,2-PUR/FS SCO BK - Sensor/actuator cable

1411970

<https://www.phoenixcontact.com/us/products/1411970>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	8

### Electrical properties

Nominal voltage $U_N$	30 V AC
	30 V DC

### Connector

#### Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	8
Locking type	SPEEDCON
Coding type	A


#### Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	8
Locking type	SPEEDCON
Coding type	A

### Cable/line

Cable length	1.2 m
--------------	-------

#### PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	46 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	8
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	8x 0.25 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.02 mm

# SAC-8P-MS/ 1,2-PUR/FS SCO BK - Sensor/actuator cable



1411970

<https://www.phoenixcontact.com/us/products/1411970>

External cable diameter	5.90 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material, filler	PE
Material wire insulation	PP
Single wire, color	white, brown, green, yellow, gray, pink, blue, red
Thickness, insulation	≥ 0.21 mm
Thickness, outer sheath	approx. 0.80 mm
Overall twist	8 wires around filler to the core
Max. conductor resistance	≤ 78 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Wave impedance	100 Ω +15 % (with 1 MHz)
Cable capacity	≤ 70 pF/m
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	8 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	48 mm
Smallest bending radius, movable installation	59 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 59 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 According to DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) Low adhesion abrasion-resistant
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish flexible
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

# SAC-8P-MS/ 1,2-PUR/FS SCO BK - Sensor/actuator cable



1411970

<https://www.phoenixcontact.com/us/products/1411970>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)