

# SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Socket, M12-SPEEDCON, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Efficient PCB assembly: two-piece connectors for SMT soldering
- SPEEDCON fast locking system reduces cabling times

## Commercial data

Item number	1414023
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB23
Product key	ABQBFC
GTIN	4055626022659
Weight per piece (including packing)	9.2 g
Weight per piece (excluding packing)	7.708 g
Customs tariff number	79070000
Country of origin	DE

# SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery

### Product properties

Product type	Circular connector housing
Thread type	M12

### Connection data

Tightening torque	1.5 ... 2 Nm
-------------------	--------------

### Material specifications

Material Housing	GD-Zn
Material Housing surface	nickel-plated
Seal material	FKM FKM
Material for screw connection	Zinc die-cast, nickel-plated

### Connector

#### Connection 1

Head design	Socket
Head thread type	M12
Head locking type	SPEEDCON

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked) IP67, when in locked state
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

# SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

## Mounting

Mounting type	Rear mounting (M15 x 1)
Assembly note	Spacing between the top edge of the PCB and the back of the front plate: 6 mm

# SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

## Classifications

### ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

### ETIM

ETIM 10.0	EC003556
-----------	----------

### UNSPSC

UNSPSC 21.0	31171600
-------------	----------

# SACC-BP-F-M12/M15-6-SMD SCO - Housing screw connection



1414023

<https://www.phoenixcontact.com/us/products/1414023>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)