

FOC-V14-F1ZNI-EM/SJO - Panel-mount frame



1413981

<https://www.phoenixcontact.com/us/products/1413981>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 panel mounting frame for transceiver, IP67, for push-pull interlocking, metal, for square mounting cutout, with seal and mounting screws

Your advantages

- High reliability with comprehensive quality assurance measures
- Intuitive front-panel operation and clear control cabinet layout thanks to uniform design

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1413981 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB17 |
| Product key | ABNODF |
| GTIN | 4055626082424 |
| Weight per piece (including packing) | 25.2 g |
| Weight per piece (excluding packing) | 18.96 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

1413981

<https://www.phoenixcontact.com/us/products/1413981>

Technical data

Product properties

| | |
|---------------------|-------------------|
| Product type | Panel-mount frame |
| Type | SC-RJ |
| Number of positions | 2 |
| Connection profile | SC-RJ |

Insulation characteristics

| | |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

Electrical properties

| | |
|---------------------|----|
| Transmission medium | FO |
|---------------------|----|

Dimensions

| | |
|--------|---------|
| Width | 22.2 mm |
| Height | 42 mm |

Mechanical characteristics

| | |
|------------------|---------|
| Ferrule diameter | 2.50 mm |
|------------------|---------|

Material specifications

| | |
|--|---------------|
| Material | Metal |
| Flammability rating according to UL 94 | V0 |
| Seal material | NBR |
| Housing material | Metal |
| Housing surface material | nickel-plated |

Cable/line

| | |
|-------------------------|----------------------|
| External cable diameter | ≤ 10.00 mm (of 5 mm) |
| Resistance to oil | yes |
| Flame resistance | yes |

Environmental and real-life conditions

Ambient conditions


| | |
|---|------------------|
| Degree of protection | IP65/IP67 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -10 °C ... 40 °C |
| Resistance to oil | yes |

Standards and regulations

| | |
|-------------------|-----|
| Flame resistance | yes |
| Resistance to oil | yes |

Drawings

Drilling plan/solder pad geometry



FOC-V14-F1ZNI-EM/SJO - Panel-mount frame



1413981

<https://www.phoenixcontact.com/us/products/1413981>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440210 |
| ECLASS-15.0 | 27440210 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002310 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

FOC-V14-F1ZNI-EM/SJO - Panel-mount frame



1413981

<https://www.phoenixcontact.com/us/products/1413981>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com