

FOC-OS12-LCD6-GF02/1 - Distributor cable




1415232

<https://www.phoenixcontact.com/us/products/1415232>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Distributor cable, degree of protection: IP20, cable length: 1 m



Your advantages

- Compact design with MT ferrule
- Push-pull interlocking
- For extreme ambient conditions

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1415232 |
| Packing unit | 1 pc |
| Minimum order quantity | 10 pc |
| Product key | ABNHAB |
| GTIN | 4055626045757 |
| Weight per piece (including packing) | 146 g |
| Weight per piece (excluding packing) | 22.22 g |
| Country of origin | PL |

1415232

<https://www.phoenixcontact.com/us/products/1415232>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Sensor type | Ethernet |
| Number of positions | 12 |
| No. of conductors | 12 |

Electrical properties

| | |
|---------------------|-----------------------|
| Attenuation | typ. 0.35 dB |
| | max. 0.6 dB |
| Transmission medium | Multi-mode fiberglass |

Mechanical properties

| | |
|---------------------------------------|---------------|
| Tensile strength short-term/long-term | 500 N / 200 N |
|---------------------------------------|---------------|

Material specifications

| | |
|------------------------|-------------------|
| Ferrule material | Zirconia ceramics |
| Outer sheath, material | LSFH |

Connector

Connection 1

| | |
|---------------------------------|---|
| Locking type | Push Pull |
| Insertion/withdrawal cycles | 500 (In the event of repeated cleaning) |
| Degree of protection | IP68 (IEC 60529) |
| Ambient temperature (operation) | -20 °C ... 70 °C (IEC 60794-1-2 F1) |

Connection 2

| | |
|----------------------|------------------|
| Locking type | Push Pull |
| Material | Plastic |
| Degree of protection | IP20 (IEC 60529) |

Cable/line

| | |
|---------------------------------------|----------------------|
| Cable length | 1 m |
| Cable weight | 8.30 kg/km |
| Cable type | Multimode fiberglass |
| Cable type | Fan out |
| Cable abbreviation | 12-.../(ZN)H-...30 |
| External cable diameter | 7 mm |
| Outer sheath, material | LSFH |
| External sheath, color | orange |
| Wire diameter incl. insulation | 250 µm |
| Individual wire diameter | 250 µm |
| Tensile strength short-term/long-term | 500 N / 200 N |

FOC-OS12-LCD6-GF02/1 - Distributor cable



1415232

<https://www.phoenixcontact.com/us/products/1415232>

| | |
|-----------------------------|------------------------------|
| Lateral pressure short term | 500.00 N/cm |
| Lateral pressure, long-term | 100.00 N/cm |
| Halogen-free | complying with IEC 60754-1/2 |

FOC-OS12-LCD6-GF02/1 - Distributor cable



1415232

<https://www.phoenixcontact.com/us/products/1415232>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27061003 |
|-------------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

FOC-OS12-LCD6-GF02/1 - Distributor cable



1415232

<https://www.phoenixcontact.com/us/products/1415232>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com