

NBC-MSX/ 2,0-94S/MSX SCO RAIL - Network cable



1415595

<https://www.phoenixcontact.com/us/products/1415595>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT6_A (10 Gbps), 8-position, PE-X halogen-free, black, shielded, Plug straight M12 SPEEDCON, coding: X / IP65, on Plug straight M12 SPEEDCON, coding: X / IP65, cable length: 2 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Securely locked by special vibration brake
- Resistant to temperature influences – tested for an extended temperature range and for resistance to temperature shocks
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1415595 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF04 |
| Product key | AF1CMJ |
| GTIN | 4055626047645 |
| Weight per piece (including packing) | 152 g |
| Weight per piece (excluding packing) | 151.9 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

1415595

<https://www.phoenixcontact.com/us/products/1415595>

Technical data

Product properties

| | |
|----------------------|-------------------------|
| Product type | Data cable preassembled |
| Application | Railway applications |
| Number of positions | 8 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Coding | X |

Interfaces

| | |
|----------------------|--------------------------------------|
| Bus system | Ethernet |
| Signal type/category | Ethernet CAT6 _A , 10 Gbps |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Electrical properties

| | |
|---|-------------------|
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |
| Nominal current I_N | 0.5 A |
| Transmission medium | Copper |
| Transmission speed | 10 Gbps |
| Transmission characteristics (category) | CAT6 _A |

Connector

Connection 1

| | |
|-----------------------------|---|
| Type | Plug straight M12 SPEEDCON / IP65 |
| Number of positions | 8 |
| Locking type | SPEEDCON |
| Coding type | X (Data) |
| Handle color | black |
| Material | CuZn (Contact) |
| | Ni/Au (Contact surface) |
| | TPU (Contact carrier) |
| | PA 6.6 (Grip body) |
| | Zinc die-cast, nickel-plated (Screw connection) |
| Standards/regulations | PA 6.6: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
| Insertion/withdrawal cycles | ≥ 100 |
| Insulation resistance | ≥ 100 MΩ |
| Tightening torque | 0.4 Nm |

NBC-MSX/ 2,0-94S/MSX SCO RAIL - Network cable



1415595

<https://www.phoenixcontact.com/us/products/1415595>

| | |
|---------------------------------|------------------|
| Degree of protection | IP65 |
| | IP67 |
| Ambient temperature (operation) | -25 °C ... 90 °C |


Connection 2

| | |
|---------------------------------|---|
| Type | Plug straight M12 SPEEDCON / IP65 |
| Number of positions | 8 |
| Locking type | SPEEDCON |
| Coding type | X (Data) |
| Handle color | black |
| Material | CuZn (Contact) |
| | Ni/Au (Contact surface) |
| | TPU (Contact carrier) |
| | PA 6.6 (Grip body) |
| | Zinc die-cast, nickel-plated (Screw connection) |
| Standards/regulations | PA 6.6: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
| Insertion/withdrawal cycles | ≥ 100 |
| Insulation resistance | ≥ 100 MΩ |
| Tightening torque | 0.4 Nm |
| Degree of protection | IP65 |
| | IP65 |
| Ambient temperature (operation) | -25 °C ... 90 °C |

Cable/line

| | |
|--------------|-----|
| Cable length | 2 m |
|--------------|-----|

Ethernet BETAtrans® railway application CAT7 [94S]

| | |
|---------------------------------|--|
| Dimensional drawing |  |
| Cable weight | 59 kg/km |
| Copper weight | 28 kg/km |
| Number of positions | 8 |
| Shielded | yes |
| Cable type | Ethernet BETAtrans® railway application CAT7 [94S] |
| Conductor structure | 4x2xAWG26/7; S/FTP |
| Signal runtime | 4.4 ns/m |
| Signal speed | 0.78 c |
| Conductor structure signal line | 7x 0.16 mm |

NBC-MSX/ 2,0-94S/MSX SCO RAIL - Network cable



1415595

<https://www.phoenixcontact.com/us/products/1415595>

| | |
|--|--|
| AWG signal line | 26 |
| Conductor cross-section | 4x 2x 0.14 mm ² |
| Wire diameter incl. insulation | 1.05 mm ±0.1 mm |
| External cable diameter | 6.60 mm ±0.2 mm |
| Outer sheath, material | PE-X |
| External sheath, color | black |
| Conductor material | Tin-plated Cu litz wires |
| Material wire insulation | Cell PE |
| Single wire, color | white-blue, white-orange, white-green, white-brown |
| Twisted pairs | 2 cores to the pair |
| Type of pair shielding | Aluminum-lined polyester foil |
| Overall twist | 4 pairs, twisted |
| Max. conductor resistance | ≤ 145 Ω/km |
| Insulation resistance | ≥ 5 GΩ*km |
| Coupling resistance | 5.00 mΩ/m (at 10 MHz) |
| Wave impedance | 100 Ω ±5 Ω (at 100 MHz) |
| Working capacitance | 44 nF (per kilometer) |
| Nominal voltage, cable | 125 V AC (U _o) |
| Test voltage Core/Core | 1000 V AC (50 Hz, 1 min.) |
| Test voltage Core/Shield | 1000.00 V AC (50 Hz, 1 min.) |
| Minimum bending radius, fixed installation | 6 x D |
| Smallest bending radius, fixed installation | 40 mm |
| Tensile strength | ≤ 60 N (temporary) ≤ 15 N (Permanent) |
| Near end crosstalk attenuation (NEXT) | 100 dB (with 1 MHz) |
| | 99 dB (at 10 MHz) |
| | 95 dB (at 100 MHz) |
| | 92 dB (at 200 MHz) |
| | 90 dB (at 250 MHz) |
| | 83 dB (at 500 MHz) |
| | 81 dB (at 600 MHz) |
| | 80 dB (at 700 MHz) |
| | 77 dB (at 800 MHz) |
| | 75 dB (at 900 MHz) |
| | 74 dB (at 1000 MHz) |
| 72 dB (at 1100 MHz) | |
| 70 dB (at 1200 MHz) | |
| Power-summated near end crosstalk attenuation (PSNEXT) | 97 dB (with 1 MHz) |
| | 96 dB (at 10 MHz) |
| | 92 dB (at 100 MHz) |
| | 89 dB (at 200 MHz) |
| | 87 dB (at 250 MHz) |
| | 80 dB (at 500 MHz) |
| | 78 dB (at 600 MHz) |

NBC-MSX/ 2,0-94S/MSX SCO RAIL - Network cable



1415595

<https://www.phoenixcontact.com/us/products/1415595>

| | |
|---|-----------------------------|
| | 77 dB (at 700 MHz) |
| | 74 dB (at 800 MHz) |
| | 72 dB (at 900 MHz) |
| | 71 dB (at 1000 MHz) |
| | 69 dB (at 1100 MHz) |
| | 67 dB (at 1200 MHz) |
| Return attenuation (RL) | 24 dB (with 1 MHz) |
| | 33.9 dB (at 10 MHz) |
| | 38.3 dB (at 100 MHz) |
| | 35.3 dB (at 200 MHz) |
| | 32.9 dB (at 250 MHz) |
| | 29.7 dB (at 500 MHz) |
| | 30.6 dB (at 600 MHz) |
| | 31 dB (at 700 MHz) |
| | 26.7 dB (at 800 MHz) |
| | 28.6 dB (at 900 MHz) |
| | 27.5 dB (at 1000 MHz) |
| | 26.9 dB (at 1100 MHz) |
| | 26.3 dB (at 1200 MHz) |
| | Crosstalk attenuation (ACR) |
| 99 dB (at 10 MHz) | |
| 93 dB (at 100 MHz) | |
| 88 dB (at 200 MHz) | |
| 86 dB (at 250 MHz) | |
| 78 dB (at 500 MHz) | |
| 74 dB (at 600 MHz) | |
| 72 dB (at 700 MHz) | |
| 69 dB (at 800 MHz) | |
| 67 dB (at 900 MHz) | |
| 65 dB (at 1000 MHz) | |
| 63 dB (at 1100 MHz) | |
| 61 dB (at 1200 MHz) | |
| Power-summated crosstalk attenuation (PS-ACR) | 97 dB (with 1 MHz) |
| | 96 dB (at 10 MHz) |
| | 90 dB (at 100 MHz) |
| | 85 dB (at 200 MHz) |
| | 83 dB (at 250 MHz) |
| | 75 dB (at 500 MHz) |
| | 71 dB (at 600 MHz) |
| | 69 dB (at 700 MHz) |
| | 66 dB (at 800 MHz) |
| | 64 dB (at 900 MHz) |
| | 62 dB (at 1000 MHz) |
| 60 dB (at 1100 MHz) | |

NBC-MSX/ 2,0-94S/MSX SCO RAIL - Network cable



1415595

<https://www.phoenixcontact.com/us/products/1415595>

| | |
|----------------------------------|---|
| Shield attenuation | 58 dB (at 1200 MHz) |
| | 0.25 dB (with 1 MHz) |
| | 0.76 dB (at 10 MHz) |
| | 2.49 dB (at 100 MHz) |
| | 3.69 dB (at 200 MHz) |
| | 4.18 dB (at 100 MHz) |
| | 5.6 dB (at 500 MHz) |
| | 6.74 dB (at 600 MHz) |
| | 7.32 dB (at 700 MHz) |
| | 7.89 dB (at 800 MHz) |
| | 8.5 dB (at 900 MHz) |
| | 9.11 dB (at 1000 MHz) |
| | 9.5 dB (at 1100 MHz) |
| | 9.9 dB (at 1200 MHz) |
| 60.00 dB (up to 1000 MHz) | |
| Halogen-free | in accordance with EN 50267-2-1 |
| | in accordance with EN 60684-2 |
| Flame resistance | in accordance with EN 60332-1-2 |
| | EN 60332-3-25 |
| | in accordance with ISO 14572 5.21 (UN ECE-R 118.01) |
| Concentration of fumes | EN 61034-2 |
| Resistance to oil | in accordance with EN 50306-4, 72 hours at 100°C, IRM 902 |
| Fire protection in rail vehicles | BS 6853 (Internal cable Ia, Ib, II/external cable Ia, Ib, II) |
| | DIN 5510-2 (Fire protection level 1, 2, 3, 4) |
| | EN 45545-2 (Risk level HL1 - HL3) |
| | EN 50306-4 |
| | NF F16-101 (Classification C/F1) |
| | NF F16-101 (Internal cable A1, A2, B/external cable A1, A2, B) |
| | NFPA 130 |
| | PN-K-02511 (Class A) |
| UIC 564-2 (Class A) | |
| Other resistance | Resistant to fuel (in accordance with EN 50306-4, 168 hours at 70°C, IRM 903) |
| | Resistant to ozone (in accordance with EN 50306-4, 72 hours at 40°C, method B, volumetric concentration of 200×10^{-6}) |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation) |

Standards and regulations

M12

| | |
|--------------------------|------------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-109 |
| Standard designation | Shock, vibration |
| Standards/specifications | EN 50155 |


Drawings

Dimensional drawing



M12 SPEEDCON plug, straight, shielded

Schematic diagram




Pin assignment of M12 plug, 8-pos., X-coded, pin side view

1415595

<https://www.phoenixcontact.com/us/products/1415595>

Circuit diagram



Contact assignment of the M12 plugs

NBC-MSX/ 2,0-94S/MSX SCO RAIL - Network cable



1415595

<https://www.phoenixcontact.com/us/products/1415595>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415595>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

NBC-MSX/ 2,0-94S/MSX SCO RAIL - Network cable



1415595

<https://www.phoenixcontact.com/us/products/1415595>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

1415595

<https://www.phoenixcontact.com/us/products/1415595>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) |
| SCIP | 3b39da27-7a1f-48f6-b55b-662ec19120f1 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 6.828 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com