

# SAC-5P- 2,0-923/FS CAN SCO - Bus system cable



1419081

<https://www.phoenixcontact.com/us/products/1419081>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, CANopen®, DeviceNet™, 5-position, PUR halogen-free, silver-gray RAL 7001, shielded, free cable end, on Socket straight M12 SPEEDCON, coding: A, cable length: 2 m, Connector unshielded

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1419081       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF04          |
| Product key                          | AF1CDD        |
| GTIN                                 | 4046356543422 |
| Weight per piece (including packing) | 131.5 g       |
| Weight per piece (excluding packing) | 135 g         |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# SAC-5P- 2,0-923/FS CAN SCO - Bus system cable



1419081

<https://www.phoenixcontact.com/us/products/1419081>

## Technical data

### Product properties

|                      |                         |
|----------------------|-------------------------|
| Product type         | Data cable preassembled |
| Application          | Standard                |
| Sensor type          | CANopen®                |
| Number of positions  | 5                       |
| No. of cable outlets | 1                       |
| Coding               | A                       |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Interfaces

|                      |                        |
|----------------------|------------------------|
| Bus system           | CANopen®/DeviceNet™    |
| Signal type/category | CANopen®<br>DeviceNet™ |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 48 V AC |
|                       | 60 V DC |
| Nominal current $I_N$ | 4 A     |
| Transmission medium   | Copper  |

### Material specifications

|  |   |
|--|---|
| Flammability rating according to UL 94 | HB  |
| Seal material                          | NBR   |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn  |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Connection data

#### Connection assignment

|   |                          |
|---|--------------------------|
| Contact   Color (signal designation)   Contact (optional) | 1 (Socket)   SR (shield) |
|   | 2 (Socket)   RD (V+)     |
|   | 3 (Socket)   BK (V-)     |
|   | 4 (Socket)   WH (CAN_H)  |

# SAC-5P- 2,0-923/FS CAN SCO - Bus system cable



1419081

<https://www.phoenixcontact.com/us/products/1419081>

|  |                         |
|--|-------------------------|
|  | 5 (Socket)   BU (CAN_L) |
|--|-------------------------|

## Connector

### Connection 1

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|


### Connection 2

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

## Cable/line

|              |     |
|--------------|-----|
| Cable length | 2 m |
|--------------|-----|

### CANopen®/DeviceNet™, PUR, gray [923]

|                                |  |
|--------------------------------|--|
| Dimensional drawing            |                                     |
| UL AWM Style                   | 21198 (80°C/300 V)   |
| Number of positions            | 4  |
| Shielded                       | yes  |
| Cable type                     | CANopen®/DeviceNet™, PUR, gray [923]   |
| Conductor structure            | 2xAWG24/19+2xAWG22/19  |
| AWG signal line                | 24   |
| AWG power supply               | 22   |
| Conductor cross-section        | 2x 0.25 mm <sup>2</sup> (Data cable)<br>2x 0.34 mm <sup>2</sup> (Power supply)<br>1x 0.34 mm <sup>2</sup> (Drain wire) |
| Wire diameter incl. insulation | 1.95 mm ±0.05 mm (Data cable)<br>1.4 mm ±0.05 mm (Power supply)  |
| External cable diameter        | 6.70 mm ±0.3 mm  |
| Outer sheath, material         | PUR  |
| External sheath, color         | silver-gray RAL 7001   |
| Conductor material             | Tin-plated Cu litz wires   |
| Material wire insulation       | Foamed PE (Data cable)<br>PE (Power supply)  |
| Single wire, color             | red-black, blue-white  |
| Twisted pairs                  | 2 cores to the pair  |
| Overall twist                  | 2 pairs around a drain wire in the center to the core  |
| Optical shield covering        | 80 %   |
| Insulation resistance          | ≥ 5 GΩ*km (Data cable)   |

# SAC-5P- 2,0-923/FS CAN SCO - Bus system cable



1419081

<https://www.phoenixcontact.com/us/products/1419081>

|   |   |
|---|---|
|   | ≥ 5 GΩ*km (Power supply)  |
| Wave impedance                                | 120 Ω ±10 % (with 1 MHz)  |
| Nominal voltage, cable                        | ≤ 300 V (Peak value, not for high-power applications)   |
| Test voltage Core/Core                        | 2000 V (50 Hz, 1 min.)  |
| Test voltage Core/Shield                      | 2000.00 V (50 Hz, 1 min.)   |
| Minimum bending radius, fixed installation    | 4 x D   |
| Minimum bending radius, flexible installation | 8 x D   |
| Dynamic load capacity (bending)               | Max. bending cycles: 5000000, Bending radius: 70 mm, Bending radius: 15 x D, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 3 m/s <sup>2</sup> , Ambient temperature: -20 °C ... 60 °C |
| Shield attenuation                            | ≤ 22.9 dB/km (with 1 MHz)   |
|   | ≤ 16.4 dB/km (At 500 kHz)   |
|   | ≤ 9.5 dB/km (At 125 kHz)  |
| Halogen-free                                  | in accordance with DIN VDE 0472 part 815  |
|   | according to IEC 60754-1  |
| Flame resistance                              | UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)  |
|   | UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)  |
|   | IEC 60332-1-2   |
|   | in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)  |
| Ambient temperature (operation)               | -40 °C ... 80 °C (cable, fixed installation)  |
|   | -30 °C ... 70 °C (Cable, flexible installation)   |
|   | -20 °C ... 60 °C (for installation)   |
|   | -20 °C ... 60 °C (cable, drag chain applications)   |

# SAC-5P- 2,0-923/FS CAN SCO - Bus system cable

1419081

<https://www.phoenixcontact.com/us/products/1419081>

## Drawings

Dimensional drawing



M12 x 1 socket, straight

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

# SAC-5P- 2,0-923/FS CAN SCO - Bus system cable



1419081

<https://www.phoenixcontact.com/us/products/1419081>

Circuit diagram



Contact assignment of the M12 socket

# SAC-5P- 2,0-923/FS CAN SCO - Bus system cable



1419081

<https://www.phoenixcontact.com/us/products/1419081>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1419081>

|  <b>UL Listed</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 125 V                 | 4 A                   | -                 | -                           |

|  <b>cUL Listed</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 125 V                 | 4 A                   | -                 | -                           |

|  <b>EAC-RoHS</b><br>Approval ID: RU D-DE.HB35.B.00387 |  |  |  |  |
|--|--|--|--|--|
|--|--|--|--|--|

# SAC-5P- 2,0-923/FS CAN SCO - Bus system cable



1419081

<https://www.phoenixcontact.com/us/products/1419081>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-5P- 2,0-923/FS CAN SCO - Bus system cable



1419081

<https://www.phoenixcontact.com/us/products/1419081>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 1.371 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)