

SAC-2X2X22-OE-OE-924-300,0 SH - Cable reel



1422116

<https://www.phoenixcontact.com/us/products/1422116>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, CANopen®, DeviceNet™, shielded, PVC, gray, 4-wire (2xAWG22 (Signal) + 2xAWG22 (Power)), color single wire: red-black, blue-white, cable length: 300 m

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1422116 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF16 |
| Product key | AF1IIC |
| GTIN | 4055626325668 |
| Weight per piece (including packing) | 22.22 g |
| Weight per piece (excluding packing) | 22.22 g |
| Customs tariff number | 85444995 |
| Country of origin | US |

SAC-2X2X22-OE-OE-924-300,0 SH - Cable reel



1422116

<https://www.phoenixcontact.com/us/products/1422116>

Technical data

Product properties

| | |
|---------------------|--------------------|
| Product type | Cable by the meter |
| Application | Connector |
| Number of positions | 5 |


Electrical properties

| | |
|-----------------------|-------|
| Nominal voltage U_N | 300 V |
|-----------------------|-------|

Cable/line

| | |
|--------------|-------|
| Cable length | 300 m |
|--------------|-------|

CANopen®/DeviceNet™, PVC, gray [924]

| | |
|-------------------------------------|---|
| Dimensional drawing |  |
| Cable weight | 64.51 kg/km |
| UL AWM Style | 2464 (80°C/300 V) |
| Number of positions | 4 |
| Shielded | yes |
| Cable type | CANopen®/DeviceNet™, PVC, gray [924] |
| Conductor structure | 2xAWG22 (Signal) + 2xAWG22 (Power) |
| Signal runtime | 4.46 ns/m |
| Conductor structure signal line | 19x 0.15 mm |
| AWG signal line | 22 |
| Conductor structure, voltage supply | 19x 0.15 mm |
| AWG power supply | 22 |
| Conductor cross-section | 2x 0.34 mm ² (Signal line) 2x 0.34 mm ² (Power supply) |
| Wire diameter incl. insulation | 1.27 mm ±0.05 mm (Signal line) 2.24 mm ±0.13 mm (Power supply) |
| External cable diameter | 6.90 mm ±0.13 mm |
| Outer sheath, material | PVC |
| External sheath, color | gray |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | Foamed PE (Signal line) PVC (Power supply) |
| Single wire, color | red-black, blue-white |

SAC-2X2X22-OE-OE-924-300,0 SH - Cable reel



1422116

<https://www.phoenixcontact.com/us/products/1422116>

| | |
|---|---|
| Twisted pairs | 2 cores to the pair |
| Type of pair shielding | Plastic-coated aluminum foil, aluminum side inside |
| Overall twist | 2 pairs around a drain wire in the center to the core |
| Insulation resistance | ≥ 59.38 Ω*m (Signal line) |
| | ≥ 57.41 GΩ*km (Power supply) |
| Wave impedance | 120 Ω ±12 Ω |
| Working capacitance | nom. 78.74 pF (per meter) |
| Minimum bending radius, flexible installation | 15 x D |
| Smallest bending radius, movable installation | 104 mm |
| Shield attenuation | 0.95 dB (f = 125 kHz) |
| | 1.64 dB (f = 500 kHz) |
| | 2.30 dB (f = 1 MHz) |
| Flame resistance | FT4 |
| Resistance to oil | yes |
| Other resistance | UV resistant |
| Special properties | UL standards PLTC and ITC |
| Ambient temperature (operation) | -30 °C ... 75 °C (cable, fixed installation) |

SAC-2X2X22-OE-OE-924-300,0 SH - Cable reel



1422116

<https://www.phoenixcontact.com/us/products/1422116>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27061801 |
| ECLASS-13.0 | 27061801 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003249 |
|-----------|----------|

1422116

<https://www.phoenixcontact.com/us/products/1422116>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | Diazene-1,2-dicarboxamide (C,C'-azodi(formamide)) (ADCA)(CAS: 123-77-3) |
|-------------------------------------|---|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com