

# HC-B16-I-TPT-M - Contact insert



1423019

<https://www.phoenixcontact.com/us/products/1423019>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 16+PE, size: B16, number of connections per position: 2, Pin, Push-in connection, 500 V, 16 A, 0.25 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, application: Power

## Your advantages

- Easy installation without tools, even when mounted, with push-in connection technology
- Shortest installation time compared to other connection technologies
- Quick and effortless wiring, in particular when space is tight
- Automatic cabling with robots possible
- Safe wiring and operation with color-coded actuators
- Shock and vibration-resistant in accordance with DIN EN 61373
- Cost-effective and fast coding with plastic profiles
- Double conductor connection per pos.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1423019       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF61          |
| Product key                          | AF7ABC        |
| GTIN                                 | 4055626322728 |
| Weight per piece (including packing) | 76.72 g       |
| Weight per piece (excluding packing) | 76.72 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | CN            |

# HC-B16-I-TPT-M - Contact insert



1423019

<https://www.phoenixcontact.com/us/products/1423019>

## Technical data

### Mounting

|               |   |
|---------------|---|
| Assembly note | To ensure correct use, installation in housing with IP54 protection or better is required |
|---------------|---|


### Product properties

|                                    |  |
|------------------------------------|--|
| Product type                       | Contact insert with a fixed no. of positions |
| Series                             | HC-B   |
| Application                        | Power  |
| Type                               | B16<br>B32                                   |
| Number of positions                | 16   |
| Connection profile                 | 16+PE  |
| Contact numbering                  | 1 - 16                                       |
| Number of connections per position | 2  |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Dimensions

|                                 |  |
|---------------------------------|--|
| Dimensional drawing             |  |
| Width                           | 34 mm  |
| Height                          | 34.6 mm  |
| Length                          | 84 mm  |
| Drill hole distance, horizontal | 77.5 mm  |

### Mechanical characteristics

|                  |        |
|------------------|--------|
| Contact diameter | 2.5 mm |
|------------------|--------|

### Connection data

#### Connection technology

|                                    |                    |
|------------------------------------|--------------------|
| Connection technology              | Push-in connection |
| Number of connections per position | 2                  |

#### Conductor connection

|                              |   |
|------------------------------|---|
| Conductor cross-section      | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Connection cross section AWG | 24 ... 16   |
| Tightening torque            | 0.8 Nm ... 1.2 Nm (PE connection)<br>0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the |

# HC-B16-I-TPT-M - Contact insert



1423019

<https://www.phoenixcontact.com/us/products/1423019>

|   |                   |
|---|-------------------|
|   | HEAVYCON housing) |
| Stripping length of the individual wire | 8 mm ±1 mm        |

## Electrical properties

|                       |       |
|-----------------------|-------|
| Rated voltage (III/3) | 500 V |
| Rated surge voltage   | 6 kV  |
| Rated current         | 16 A  |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

## Material specifications

|  |              |
|--|--------------|
| Flammability rating according to UL 94 | V0           |
| Contact material                       | Copper alloy |
| Contact surface material               | Ag           |
| Contact carrier material               | PC           |
| Standards/regulations                  | PC           |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

## Standards and regulations

|  |              |
|--|--------------|
| Constructional and testing regulations | DIN EN 61984 |
|  | DIN EN 60664 |
|  | IEC 60352    |
| Tests                                  | DIN EN 61984 |
|  | DIN EN 60664 |
|  | IEC 60352    |

### Testing

|                       |   |
|-----------------------|---|
| Standards/regulations | PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
|-----------------------|---|


# HC-B16-I-TPT-M - Contact insert

1423019

<https://www.phoenixcontact.com/us/products/1423019>


## Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Mounting cutout when used without housing

# HC-B16-I-TPT-M - Contact insert

1423019

<https://www.phoenixcontact.com/us/products/1423019>



Schematic diagram



Connector pin assignment, connection side

# HC-B16-I-TPT-M - Contact insert

1423019


<https://www.phoenixcontact.com/us/products/1423019>

## Schematic diagram



Coding options

## Diagram



Derating diagram

# HC-B16-I-TPT-M - Contact insert



1423019

<https://www.phoenixcontact.com/us/products/1423019>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1423019>

### DNV

Approval ID: TAE000037S



### CSA

Approval ID: 13631

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 600 V                 | 11 A                  | - 16              | -                           |



### UL Recognized

Approval ID: E118976

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 600 V                 | 14 A                  | - 16              | -                           |

# HC-B16-I-TPT-M - Contact insert



1423019

<https://www.phoenixcontact.com/us/products/1423019>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440205 |
| ECLASS-15.0 | 27440205 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000438 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121500 |
|-------------|----------|

# HC-B16-I-TPT-M - Contact insert



1423019

<https://www.phoenixcontact.com/us/products/1423019>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)