

# CUC-V14-C1ZNI-T/R4E8:10 - RJ45 connector



1422679

<https://www.phoenixcontact.com/us/products/1422679>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Push-pull connector (version 14), die-cast zinc, with RJ45 connector insert, 8-pos., with IDC fast connection technology, for 1 and 7-wire cores, 26 ... 24 AWG, for cable diameter of 5.5 mm ... 10 mm

## Your advantages

- Push-pull ADVANCE connector
- Locking system to prevent inadvertent release
- Protected data transmission thanks to 360° shielding concept
- Highest ESD and EMC resistance for reliable transmission

## Commercial data

Item number	1422679
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AB17
Product key	ABNOAA
GTIN	4055626311418
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85366990
Country of origin	DE

# CUC-V14-C1ZNI-T/R4E8:10 - RJ45 connector



1422679

<https://www.phoenixcontact.com/us/products/1422679>

## Technical data

### Product properties

Product type	Data plug
Type	Version 14
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Cable outlet	angled

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Frequency range	to 100 MHz
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

### Connection data

Connection method	IDC fast connection
-------------------	---------------------

### Dimensions

Width	22 mm
Height	50 mm
Length	80 mm

### Material specifications

Seal material	NBR
Housing material	Die-cast zinc
Housing surface material	nickel-plated

### Cable/line

External cable diameter	5.5 mm ... 10 mm
External cable diameter	5.5 mm ... 10 mm

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 750
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

# CUC-V14-C1ZNI-T/R4E8:10 - RJ45 connector



1422679

<https://www.phoenixcontact.com/us/products/1422679>

Ambient temperature (assembly)

-10 °C ... 40 °C

# CUC-V14-C1ZNI-T/R4E8:10 - RJ45 connector



1422679

<https://www.phoenixcontact.com/us/products/1422679>

## Classifications

### UNSPSC

UNSPSC 21.0	39121409
-------------	----------

# CUC-V14-C1ZNI-T/R4E8:10 - RJ45 connector



1422679

<https://www.phoenixcontact.com/us/products/1422679>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)