

MH-25-MULTI-65-PV-BK - Cable feed-through plates



1424582

<https://www.phoenixcontact.com/us/products/1424582>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable feed-through plates, no. of conductors: 25, external cable diameter: 3x 3 mm ... 6 mm, 9x 3 mm ... 7 mm, 8x 6 mm ... 9 mm, 4x 6 mm ... 12 mm, 1x 10 mm ... 20 mm, material: PP (Core), material: TPE-SEBS (external material), color: black, length: 154 mm, width: 56 mm, height: 20 mm

Your advantages

- The panel cutouts of size B24 heavy-duty connectors can be used.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1424582 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF67 |
| Product key | AF7CAX |
| GTIN | 4055626374857 |
| Weight per piece (including packing) | 80.7 g |
| Weight per piece (excluding packing) | 79.2 g |
| Customs tariff number | 39269097 |
| Country of origin | FI |

MH-25-MULTI-65-PV-BK - Cable feed-through plates



1424582

<https://www.phoenixcontact.com/us/products/1424582>

Technical data


Product properties

| | |
|-------------------|--------------------|
| Product type | Cable feed-through |
| No. of conductors | 25 |

Connection data

| | |
|-------------------------|------------------|
| External cable diameter | 3x 3 mm ... 6 mm |
| Tightening torque | 1.8 Nm |

Dimensions

| | |
|---------------------------------|---|
| Dimensional drawing |  |
| Width | 56 mm |
| Height | 20 mm |
| Length | 154 mm |
| Drill hole distance, horizontal | 130 mm |
| Drill hole distance, vertical | 32 mm |
| Hole diameter | 4 mm |

Material specifications

| | |
|--|------------------------------|
| Color | black (RAL 9005) |
| Material interior | PP (Core) |
| Material exterior | TPE-SEBS (external material) |
| Flammability rating according to UL 94 | V0 |

Cable/line

| | |
|-------------------------|--------------------|
| External cable diameter | 3x 3 mm ... 6 mm |
| | 9x 3 mm ... 7 mm |
| | 8x 6 mm ... 9 mm |
| | 4x 6 mm ... 12 mm |
| | 1x 10 mm ... 20 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP65 |
| Ambient temperature (operation) | -40 °C ... 90 °C |

1424582

<https://www.phoenixcontact.com/us/products/1424582>

Mounting

| | |
|---------------|--|
| Assembly note | <p>M4 mounting screw, torque: 1.8 Nm, SW5 Allen key</p> <p>The mounting screws provided are to be used for mounting.</p> <p>Mounting sequence:</p> <ol style="list-style-type: none">1) Fix Multigates with the mounting screws provided (observe torque)2) Cut a hole in the membrane/cut off the tip of the cone3) Guide the cable through the opening (from the outside). Withdraw the cable approximately 20 mm (to improve strain relief) |
|---------------|--|

MH-25-MULTI-65-PV-BK - Cable feed-through plates




1424582

<https://www.phoenixcontact.com/us/products/1424582>

Drawings

Dimensional drawing




Dimensional drawing

MH-25-MULTI-65-PV-BK - Cable feed-through plates



1424582

<https://www.phoenixcontact.com/us/products/1424582>



Wall cutout drawing

MH-25-MULTI-65-PV-BK - Cable feed-through plates



1424582

<https://www.phoenixcontact.com/us/products/1424582>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424582>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

MH-25-MULTI-65-PV-BK - Cable feed-through plates



1424582

<https://www.phoenixcontact.com/us/products/1424582>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400569 |
| ECLASS-15.0 | 27400569 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001004 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31163000 |
|-------------|----------|

MH-25-MULTI-65-PV-BK - Cable feed-through plates



1424582

<https://www.phoenixcontact.com/us/products/1424582>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com